

88777 Multi-Conductor - CMP Rated (Plenum) Cable

For more Information
please call

1-800-Belden1

**General Description:**

22 AWG stranded (7x30) TC conductor, FEP insulation, twisted pairs individually shielded with Beldfoil® (100% coverage), overall jacket per table below, 22 AWG stranded TC drain wire.

Physical Characteristics (Overall)**Conductor**

AWG:

# Pairs	AWG	Stranding	Conductor Material	Dia. (mm)
3	22	7x30	TC - Tinned Copper	0.762

Total Number of Conductors: 6

Insulation

Insulation Material:

Insulation Trade Name	Insulation Material	Wall Thickness (mm)
Teflon®	FEP - Fluorinated Ethylene Propylene	0.254

Inner Shield

Inner Shield Material:

Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
Beldfoil® (Z-Fold®)	Tape	Aluminum Foil-Polyester Tape	100

Inner Shield Drain Wire AWG:

AWG
22

Inner Shield Drain Wire Stranding: 16x34

Inner Shield Drain Wire Conductor Material: TC - Tinned Copper

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Trade Name	Outer Jacket Material	Nom. Wall Thickness (mm)
Teflon®	FEP - Fluorinated Ethylene Propylene	0.356

Overall Cable

Overall Nominal Diameter: 5.944 mm

Pair

Pair Color Code Chart:

Number	Color
1	Black & Red
2	Black & White
3	Black & Green

Mechanical Characteristics (Overall)

Operating Temperature Range: -70°C To +200°C

Bulk Cable Weight: 55.063 Kg/Km

Max. Recommended Pulling Tension: 364.752 N

Min. Bend Radius/Minor Axis: 63.500 mm

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification: CMP

CEC/C(UL) Specification: CMP

METRIC MEASUREMENT VERSION

88777 Multi-Conductor - CMP Rated (Plenum) Cable

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 04/01/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MIL Order #39 (China RoHS): Yes

Flame Test

UL Flame Test: NFPA 262

CSA Flame Test: FT6

Plenum/Non-Plenum

Plenum (Y/N): Yes

Non-Plenum Number: 8777

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

50

Nom. Inductance:

Inductance (µH/m)

0.59058

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)

101.711

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/m)

219.827

Nominal Velocity of Propagation:

VP (%)

69

Maximum Conductor DC Resistance:

DCR @ 20°C (Ohm/100 m)

52.496

Ind. Pair Nominal Shield DC Resistance @ 20 Deg. C: 37.075 Ohm/km

Max. Operating Voltage - UL:

Voltage

300 V RMS

Max. Recommended Current:

Current

1.96 Amps per conductor @ 25°C

Notes (Overall)

Notes: Teflon® is a registered trademark of E. I. duPont de Nemours and Co. used under license by Belden, Inc.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
88777 002100	30 MT	2.676 KG	RED	C	3 SH PR #22 FEP FEP
88777 0021000	305 MT	18.597 KG	RED	C	3 SH PR #22 FEP FEP
88777 002500	152 MT	9.072 KG	RED	C	3 SH PR #22 FEP FEP
88777 0025000	1,524 MT	88.451 KG	RED		3 SH PR #22 FEP FEP

Notes:

C = CRATE REEL PUT-UP.

88777 Multi-Conductor - CMP Rated (Plenum) Cable

Revision Number: 2 Revision Date: 08-16-2012

© 2014 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.