





PRODUCT NO.

SEE TABLE



NOTES:

- ① MOLDING MATERIAL: MODIFIED POLYPHENYLENE ETHER, FLAME RETARDANT PER UL 94 V-0, COLOR: BLACK.
- ② RETENTION ROD MATERIAL: STREN NYLON .030/0.76 DIA. QUANTITY OF RETENTION RODS IS TWO(2) PER HOUSING.
3. PIN LENGTH TO BE .210/5.33 MIN RECOMMENDED PIN LENGTH IS .225±.015/5.72±.38
4. PRODUCT SPECIFICATION: BUS-12-067.
5. PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
6. THIS PRODUCT IS NOT INTENDED TO BE EXPOSED TO MANUFACTURING SOLDER PROCESSES.



|                               |          |     |            |         |                                       |            |                           |
|-------------------------------|----------|-----|------------|---------|---------------------------------------|------------|---------------------------|
| mat'l. code<br>SEE NOTE 1 & 2 |          |     |            | surface | tolerance                             | projection | product family            |
| ltr                           | ec'n no  | dr  | date       |         | tolerances unless otherwise specified |            | PV HOUSINGS               |
| H                             | v07-0563 | HTB | 2007-08-27 | angles  | linear                                | INCH/MM    | title                     |
| -                             | -        | -   | -          |         |                                       |            | MINI ROD HSG DR POLARIZED |
| C                             | v60450   | SAR | 1996-03-13 | 0°±2'   |                                       | scale 2:1  | .100 [2.54] CC WITH RODS  |
| D                             | v91206   | BKB | 1999-07-06 | dr      | R. SIEPLE                             | 1988-09-27 | dwg no                    |
| E                             | v03-1336 | PJ  | 2004-01-22 | engr    | H. SUNDY                              | 1988-09-27 | sheet 1 of 2              |
| F                             | v05-0717 | TAB | 2005-07-29 | chr     | H. SUNDY                              | 1989-07-07 | size                      |
| G                             | v06-0448 | HTB | 2006-05-22 | appd    | H. SUNDY                              | 1989-07-07 | A3                        |
| sheet                         | revision | H   | H          |         |                                       |            | type                      |
| index                         | sheet    | 1   | 2          |         |                                       |            | Product Customer Drawing  |



FCconnect.com

Copyright FCI

| PRODUCT NO. | NO OF POS | DIM K       | DIM L       | DIM C     | RETENTION ROD P/N | RETENTION ROD LENGTH |
|-------------|-----------|-------------|-------------|-----------|-------------------|----------------------|
| 86805-001LF | 2 X 12    | 1.200/30.48 | 1.100/27.94 | .115/2.92 | 65048-026         | 2.300/58.42          |
| 86805-002LF | 2 X 15    | 1.500/38.10 | 1.400/35.56 | .115/2.92 | 65048-026         | 2.300/58.42          |
| 86805-003LF | 2 X 19    | 1.900/48.26 | 1.800/45.72 | .115/2.92 | 65048-026         | 2.300/58.42          |
| 86805-004LF | 2 X 22    | 2.200/55.88 | 2.100/53.34 | .115/2.92 | 65048-013         | 3.450/87.63          |
| 86805-005LF | 2 X 27    | 2.700/68.58 | 2.600/66.04 | .115/2.92 | 65048-013         | 3.450/87.63          |
| 86805-006LF | 2 X 10    | 1.000/25.40 | .900/22.86  | .115/2.92 | 65048-026         | 2.300/58.42          |
| 86805-007LF | 2 X 7     | .700/17.78  | .600/15.24  | .115/2.92 | 65048-040         | 1.300/33.02          |
| 86805-008LF | 2 X 9     | .900/22.86  | .800/20.32  | .115/2.92 | 65048-040         | 1.300/33.02          |
| 86805-009LF | 2 X 32    | 3.200/81.28 | 3.100/78.74 | .115/2.92 | 65048-005         | 4.650/118.11         |
| 86805-010LF | 2 X 5     | .500/12.70  | .400/10.16  | .115/2.92 | 65048-040         | 1.300/33.02          |
| 86805-011LF | 2 X 8     | .800/20.32  | .700/17.78  | .115/2.92 | 65048-040         | 1.300/33.02          |
| 86805-012LF | 2 X 25    | 2.500/63.50 | 2.400/60.96 | .115/2.92 | 65048-013         | 3.450/87.63          |
| 86805-013LF | 2 X 30    | 3.000/76.20 | 2.900/73.66 | .115/2.92 | 65048-005         | 4.650/118.11         |
| 86805-014LF | 2 X 2     | .200/5.08   | .100/2.54   | .115/2.92 | 65048-040         | 1.300/33.02          |
| 86805-015LF | 2 X 3     | .300/7.62   | .200/5.08   | .115/2.92 | 65048-040         | 1.300/33.02          |
| 86805-016LF | 2 X 4     | .400/10.16  | .300/7.62   | .115/2.92 | 65048-040         | 1.300/33.02          |
| 86805-017LF | 2 X 6     | .600/15.24  | .500/12.70  | .115/2.92 | 65048-040         | 1.300/33.02          |
| 86805-018LF | 2 X 11    | 1.100/27.94 | 1.000/25.40 | .115/2.92 | 65048-026         | 2.300/58.42          |
| 86805-019LF | 2 X 13    | 1.300/33.02 | 1.200/30.48 | .115/2.92 | 65048-026         | 2.300/58.42          |
| 86805-020LF | 2 X 14    | 1.400/35.58 | 1.300/33.02 | .115/2.92 | 65048-026         | 2.300/58.42          |
| 86805-021LF | 2 X 16    | 1.600/40.64 | 1.500/38.10 | .115/2.92 | 65048-026         | 2.300/58.42          |
| 86805-022LF | 2 X 17    | 1.700/43.18 | 1.600/40.64 | .115/2.92 | 65048-026         | 2.300/58.42          |
| 86805-023LF | 2 X 18    | 1.800/45.72 | 1.700/43.18 | .115/2.92 | 65048-026         | 2.300/58.42          |
| 86805-024LF | 2 X 20    | 2.000/50.80 | 1.900/48.26 | .115/2.92 | 65048-013         | 3.450/87.63          |
| 86805-025LF | 2 X 21    | 2.100/53.34 | 2.000/50.80 | .115/2.92 | 65048-013         | 3.450/87.63          |
| 86805-026LF | 2 X 23    | 2.300/58.42 | 2.200/55.88 | .115/2.92 | 65048-013         | 3.450/87.63          |
| 86805-027LF | 2 X 24    | 2.400/60.96 | 2.300/58.42 | .115/2.92 | 65048-013         | 3.450/87.63          |
| 86805-028LF | 2 X 26    | 2.600/66.04 | 2.500/63.50 | .115/2.92 | 65048-013         | 3.450/87.63          |
| 86805-029LF | 2 X 28    | 2.800/71.12 | 2.700/68.58 | .115/2.92 | 65048-013         | 3.450/87.63          |
| 86805-030LF | 2 X 29    | 2.900/73.66 | 2.800/71.12 | .115/2.92 | 65048-013         | 3.450/87.63          |
| 86805-031LF | 2 X 31    | 3.100/78.74 | 3.000/76.20 | .115/2.92 | 65048-005         | 4.650/118.11         |
| 86805-032LF | 2 X 33    | 3.300/83.82 | 3.200/81.28 | .115/2.92 | 65048-005         | 4.650/118.11         |
| 86805-033LF | 2 X 34    | 3.400/86.36 | 3.300/83.82 | .115/2.92 | 65048-005         | 4.650/118.11         |
| 86805-034LF | 2 X 35    | 3.500/89.90 | 3.400/86.36 | .115/2.92 | 65048-005         | 4.650/118.11         |
| 86805-035LF | 2 X 36    | 3.600/91.44 | 3.500/88.90 | .115/2.92 | 65048-005         | 4.650/118.11         |
| 86805-036LF | 2 X 3     | .300/7.62   | .200/5.08   | .075/1.91 | 65048-040         | 1.300/33.02          |

|                               |          |    |      |                                                       |           |                   |  |                               |              |
|-------------------------------|----------|----|------|-------------------------------------------------------|-----------|-------------------|--|-------------------------------|--------------|
| mat'l. code<br>SEE NOTE 1 & 2 |          |    |      | surface <input checked="" type="checkbox"/> tolerance |           | projection        |  | product family<br>PV HOUSINGS |              |
| ltr                           | ecn no   | dr | date | tolerances unless otherwise specified                 |           |                   |  | title                         |              |
| H                             |          |    |      | angles                                                | linear    | .XX+01/XX+3       |  | MINI ROD HSG DR POLARIZED     |              |
|                               |          |    |      |                                                       |           | .XXX+005/XXX+13   |  | .100 [2.54] CC WITH RODS      |              |
|                               |          |    |      | 0°±2°                                                 |           | XXXX+0020/XXX+051 |  | scale 2:1                     |              |
|                               |          |    |      | dr                                                    | R. SIEPLE | 1988-09-27        |  |                               | dwg no       |
|                               |          |    |      | engr                                                  | H. SUNDY  | 1988-09-27        |  |                               | sheet 2 of 2 |
|                               |          |    |      | chr                                                   | H. SUNDY  | 1989-07-07        |  |                               | A3           |
|                               |          |    |      | appd                                                  | H. SUNDY  | 1989-07-07        |  |                               |              |
| sheet                         | revision |    |      |                                                       |           |                   |  |                               |              |
| index                         | sheet    |    |      |                                                       |           |                   |  |                               |              |