

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT — By —

ALL RIGHTS RESERVED.

ÄNDERUNGEN DIE DEM TECH-
NISCHEN FORTSCHRITT DIENEN,
BEHALTEN WIR UNS VOR

CAD—ORIGINAL
ZEICHNUNG NICHT ÄNDERN

GEGENSTECKER/KONTAKT: ☒

MATED WITH: 825 433

☒ 167 301—4

ZEICHNUNG GESCHÜTZT DURCH
© COPYRIGHT 1975
AMP DEUTSCHLAND GMBH
ALLE RECHTE VORBEHALTEN

1

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI

2.94

14.2

2.5

EINREIHIG

POLZ.	L±0.8	BESTELL—NR.
—	—	—
2	5.08	925 369 —2
3	7.62	—3
4	10.16	—4
5	12.70	—5
6	15.24	—6
7	17.78	—7
8	20.32	—8
9	22.86	—9
10	25.40	1— —0
11	27.94	1— —1
12	30.48	1— —2
13	33.02	1— —3
14	35.56	1— —4
15	38.10	1— —5
16	40.64	1— —6
17	43.18	1— —7
18	45.72	1— —8
19	48.26	1— —9
20	50.80	2— —0
21	53.34	2— —1
22	55.88	2— —2
23	58.42	2— —3
24	60.96	2— —4
25	63.50	2— —5
26	66.04	2— —6
27	68.58	2— —7
28	71.12	2— —8
29	73.66	2— —9
30	76.20	3— —0
31	78.74	3— —1
32	81.28	3— —2
33	83.82	3— —3
34	86.36	3— —4
35	88.90	3— —5
36	91.44	3— —6
37	93.98	3— —7
38	96.52	3— —8
39	99.06	3— —9
40	101.60	4— —0
41	104.14	4— —1
42	106.68	4— —2
43	109.22	4— —3
44	111.76	4— —4
45	114.30	4— —5
46	116.84	4— —6
47	119.38	4— —7
48	121.92	4— —8
49	124.46	4— —9
50	127.00	5— 925 369 —0

POLZAHLx2.54 ±0.8

2.54 ±0.1

RAST—NOPPENSTELLUNG WECHSELT PRODUKTIONSBEDINGT.
NOPPEN VERRASTEN ENTSPRECHEND LINKS ODER RECHTS MIT STIFTLAISTE.

POSITIONS OF LOCKING DEVICE CHANGED CONDITIONAL OF PRODUCTION.
KNUPS LOCK ACCORDING ON THE LEFT OR RIGHT SIDE WITH PIN HEADER.

GRÜN RAL6011

OBERFLÄCHE

FARBE

WAR

75—9226

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± —

1 PLC ± —

2 PLC ± 0.2mm

3 PLC ± —

4 PLC ± —

ANGLES ± —

FINISH —

MATERIAL

PA 6.6

DWN DAHLHEIMER 05.12.75

CHK KREPP

APVD —

PRODUCT SPEC —

APPLICATION SPEC —

WEIGHT —

CUSTOMER DRAWING

NAME

AMPMODU IV GEHAEUSE,
EINREIHIG

SIZE A3

CAGE CODE 00779

DRAWING NO C—925369

RESTRICTED TO —

SCALE —

SHEET 1 OF 1

REV W1

1470—19 (3/11)