


CONTACT CONFIGURATION
TIMING (BBM) NON-SHORTING



B
Ø26.00
[1.024 in]

27.50
[1.083 in]



HARDWARE SUPPLIED ▲
ON SWITCH

8.00
[.315 in]

9.50
[.374 in]

5.50
[.217 in]
FLAT



3/8-32 UNEF-2A
THREADS

2.00
[.079 in]

14.20
[.559 in]

18.80
[.740 in]

B
6.60
[.260 in]



NOTE:

1. ALL DIMENSIONS IN MM[INCH].
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. CONTACT MATERIAL: SILVER
5. CONTACT RATING: 150MILLIAMP, 250VAC/DC
350MILLIAMP, 110VAC/DC
6. CONTACT RATING (NON-SWITCHING) 5A
7. OPERATING FORCE 425±100CM/STANDARD
8. OPERATING TEMP: -30°C TO 85°C
- ▲ 9. CIRCUIT DP: 5 POSITION 30° INDEX.
10. DIELECTRIC STRENGTH: 1000V RMS MIN.@ SEA LEVEL.
- ▲ 11. HARDWARE SUPPLIED ON SWITCH:
LOCKWASHER, HEXNUT, STOP RING
12. ▲ DENOTES CRITICAL PARAMETER.
- 13 2002/95/EC (RoHS) COMPLIANT



C	19363	UPDATED NOTES	10/18/10	BMA
B	14486	UPDATE DIMS	11/10/04	AR
A	14007	RELEASED FOR PRODUCTION	5/18/04	AR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



TITLE KC25A9.501NLS

SCALE 1.5:1

DATE 5/18/2004

DR AR

DWG G510582

REV C