


TUM/TUW Series

Ceramic Housed Axial Terminal Power



Series	Wattage	Ohms	Dimensions (in. / mm)			Voltage	Element
			Length (±1mm)	Height (±1mm)	Width (±1mm)		
TUW3	3	0.01-39	0.87 / 22	0.31 / 8	0.31 / 8	350	Wirewound
TUW5	5	0.01-47	0.87 / 22	0.35 / 9	0.39 / 10	350	Wirewound
TUW7	7	0.10-680	1.48 / 35	0.35 / 9	0.39 / 10	500	Wirewound
TUW10	10	0.10-990	1.93 / 49	0.35 / 9	0.39 / 10	750	Wirewound
TUW15	15	0.10-1000	1.93 / 49	.453/11.5	0.49 / 12.5	1000	Wirewound
TUM3	3	180-33K	0.87 / 22	0.31 / 8	0.31 / 8	350	Metal oxide
TUM5	5	220-50K	0.87 / 22	0.35 / 9	0.39 / 10	350	Metal oxide
TUM7	7	910-50K	1.48 / 35	0.35 / 9	0.39 / 10	500	Metal oxide
TUM10	10	1000-50K	1.93 / 49	0.35 / 9	0.39 / 10	750	Metal oxide
TUM15	15	1100-150K	1.93 / 49	.453/11.5	0.49 / 12.5	1000	Metal oxide


The TUM/TUW Series resistors are our most economical power resistors. They are recommended for commercial applications where low cost is critical.

They are available in small standard packs for standard values, or bulk packaged for even lower costs.

FEATURES

- Economical Commercial Grade for general purpose use
- Wirewound and Metal Oxide construction
- Wide resistance range
- Flameproof inorganic construction

DERATING CURVE



SPECIFICATIONS

Material

Housing: Ceramic

Core: Fiberglass or metal oxide

Filling: Cement based

Electrical

Tolerance: 5% standard

Temperature coeff.:

0.01-20Ω ±400ppm/°C

20-150KΩ ±350ppm/°C

Dielectric withstanding voltage:
1,000VAC

Short time overload

TUW: 10x rated power for 5 sec.

TUM: 5x rated power for 5 sec.

ORDERING INFORMATION

TUM 3 J 8 R 2 E		
Series	Wattage	Resistance Value
TUM = Ceramic Housed	3	Example:
Metal Oxide	5	R50=0.50Ω
TUW = Ceramic Housed	7	1R0=1Ω
Wirewound	10	8R2=8.2Ω
	15	250=250Ω
		1K0=1,000Ω
		8K2=8,200Ω
		10K=10,000Ω

STANDARD PART NUMBERS FOR TUW/TUM SERIES

Ohmic value	Part No. Prefix Suffix	Wattage					Ohmic value	Part No. Prefix Suffix	Wattage					Ohmic value	Part No. Prefix Suffix	Wattage					Ohmic value	Part No. Prefix Suffix	Wattage				
		TUW3J	TUW5J	TUW7J	TUW10J	TUW15J			TUW3J	TUW5J	TUW7J	TUW10J	TUW15J			TUW3J	TUW5J	TUW7J	TUW10J	TUW15J			TUW3J	TUW5J	TUW7J	TUW10J	TUW15J
0.01	R01E	✓	✓				1.0	1R0E	✓	✓	✓	✓	✓	680	680E	✓	✓	✓	✓	✓	33	33RE	✓	✓	✓	✓	✓
0.01	R01E	✓	✓				1.5	1R5E	✓	✓	✓	✓	✓	750	750E	✓	✓	✓	✓	✓	39	39RE	✓	✓	✓	✓	✓
0.02	R02E	✓	✓				2.0	2R0E	✓	✓	✓	✓	✓	820	820E	✓	✓	✓	✓	✓	43	43RE	✓	✓	✓	✓	✓
0.04	R04E	✓	✓				2.7	2R7E	✓	✓	✓	✓	✓	1000	1K0	✓	✓	✓	✓	✓	47	47RE	✓	✓	✓	✓	✓
0.05	R05E	✓	✓				3.0	3R0E	✓	✓	✓	✓	✓	1500	1K5	✓	✓	✓	✓	✓	56	56RE	✓	✓	✓	✓	✓
0.10	R10E	✓	✓	✓	✓	✓	3.3	3R3E	✓	✓	✓	✓	✓	2000	2K0	✓	✓	✓	✓	✓	68	68RE	✓	✓	✓	✓	✓
0.15	R15E	✓	✓	✓	✓	✓	3.9	3R9E	✓	✓	✓	✓	✓	2700	2K7	✓	✓	✓	✓	✓	75	75RE	✓	✓	✓	✓	✓
0.20	R20E	✓	✓	✓	✓	✓	4.3	4R3E	✓	✓	✓	✓	✓	3000	3K0	✓	✓	✓	✓	✓	82	82RE	✓	✓	✓	✓	✓
0.27	R27E	✓	✓	✓	✓	✓	4.7	4R7E	✓	✓	✓	✓	✓	3300	3K3	✓	✓	✓	✓	✓	100	100E	✓	✓	✓	✓	✓
0.30	R30E	✓	✓	✓	✓	✓	5.6	5R6E	✓	✓	✓	✓	✓	3900	3K9	✓	✓	✓	✓	✓	150	150E	✓	✓	✓	✓	✓
0.33	R33E	✓	✓	✓	✓	✓	6.8	6R8E	✓	✓	✓	✓	✓	4300	4K3	✓	✓	✓	✓	✓	200	200E	✓	✓	✓	✓	✓
0.39	R39E	✓	✓	✓	✓	✓	7.5	7R5E	✓	✓	✓	✓	✓	4700	4K7	✓	✓	✓	✓	✓	270	270E	✓	✓	✓	✓	✓
0.43	R43E	✓	✓	✓	✓	✓	8.2	8R2E	✓	✓	✓	✓	✓	5600	5K6	✓	✓	✓	✓	✓	300	300E	✓	✓	✓	✓	✓
0.47	R47E	✓	✓	✓	✓	✓	10	10RE	✓	✓	✓	✓	✓	6800	6K8	✓	✓	✓	✓	✓	330	330E	✓	✓	✓	✓	✓
0.56	R56E	✓	✓	✓	✓	✓	15	15RE	✓	✓	✓	✓	✓	7500	7K5	✓	✓	✓	✓	✓	390	390E	✓	✓	✓	✓	✓
0.68	R68E	✓	✓	✓	✓	✓	20	20RE	✓	✓	✓	✓	✓	8200	8K2	✓	✓	✓	✓	✓	430	430E	✓	✓	✓	✓	✓
0.75	R75E	✓	✓	✓	✓	✓	27	27RE	✓	✓	✓	✓	✓	10000	10K	✓	✓	✓	✓	✓	470	470E	✓	✓	✓	✓	✓
0.82	R82E	✓	✓	✓	✓	✓	30	30RE	✓	✓	✓	✓	✓								560	560E	✓	✓	✓	✓	✓

Check product availability at www.ohmite.com

Shaded area: change prefix to TUM