

■ FEATURES

HFI chip inductors are Jaro's line of high frequency ceramic chip inductors. We have developed highly reliable and versatile chip inductors that will meet your high frequency design requirements.

• High Frequency Range

HFI chip inductors have a ceramic material construction that extends the effective frequency range to 10GHz.

• Multiple Size Availability

HFI chip inductors are available in three compact sizes: 060303, 100505, 160808 and 201209.

• High Q characteristics

H-series HFI chip inductors exhibit higher Q at high frequency.

■ APPLICATIONS

HFI chip inductors can be used in a variety of electronics including:

- Cellular Phones
- Pager
- High-Speed Communication Devices
- WALN and RF module

■ PRODUCT IDENTIFICATION

1 2 3 4 5 6
HFI - 160808 - 1N2 S □ □ -P

Product Code

Dimensions (in mm)

Inductance Code


Tolerance Code

Pattern Code

RoHS Code

Code	Tolerance
G	$\pm 2\%$
J	$\pm 5\%$
K	$\pm 10\%$
C	$\pm 0.2\text{nH}$
S	$\pm 0.3\text{nH}$

■ PRODUCT DIMENSIONS



PRODUCT NO.	A	B	C	D
HFI-201209 (0805)	2.0 ± 0.20 (0.079 ± 0.008)	1.2 ± 0.20 (0.047 ± 0.008)	0.9 ± 0.20 (0.035 ± 0.008)	0.5 ± 0.30 (0.020 ± 0.012)
HFI-160808 (0603)	1.6 ± 0.15 (0.063 ± 0.006)	0.8 ± 0.15 (0.031 ± 0.006)	0.8 ± 0.15 (0.031 ± 0.006)	0.3 ± 0.20 (0.012 ± 0.008)
HFI-100505 (0402)	1.0 ± 0.10 (0.039 ± 0.004)	0.5 ± 0.10 (0.020 ± 0.004)	0.5 ± 0.10 (0.020 ± 0.004)	0.25 ± 0.10 (0.010 ± 0.004)
HFI-060303 (0201)	0.6 ± 0.03 (0.024 ± 0.001)	0.33max. (0.012max.)	0.33max. (0.012max.)	0.15 ± 0.05 (0.006 ± 0.002)


■ PRODUCT SPECIFICATIONS

PART NUMBER	Inductance (nH) at 100 MHz	Tolerance	Q Min.	Q Typical			S.R.F.(MHz) Min.	R _{DC} (Ω) Max.	Rated Current (mA) Max.
			100 MHz	100 MHz	500 MHz	800 MHz			
HFI-060303-0N3□	0.3	C	4	5	13	18	10000	0.07	250
HFI-060303-0N4□	0.4	C	4	5	13	18	10000	0.07	250
HFI-060303-0N5□	0.5	C	4	5	13	18	10000	0.08	250
HFI-060303-0N6□	0.6	C	4	5	13	18	10000	0.08	250
HFI-060303-0N7□	0.7	C	4	5	13	18	10000	0.09	250
HFI-060303-0N8□	0.8	C	4	5	13	18	10000	0.10	250
HFI-060303-0N9□	0.9	C	4	5	13	18	10000	0.10	250
HFI-060303-1N0□	1.0	C,S	4	5	15	19	10000	0.14	250
HFI-060303-1N1□	1.1	C,S	4	6	15	20	10000	0.14	250
HFI-060303-1N2□	1.2	C,S	4	6	15	20	10000	0.14	250
HFI-060303-1N3□	1.3	C,S	4	6	15	20	10000	0.14	250
HFI-060303-1N5□	1.5	C,S	4	6	15	20	10000	0.18	230
HFI-060303-1N6□	1.6	C,S	4	6	15	20	10000	0.18	230
HFI-060303-1N8□	1.8	C,S	4	6	15	20	10000	0.19	200
HFI-060303-2N0□	2.0	C,S	4	6	15	20	8800	0.20	200
HFI-060303-2N2□	2.2	C,S	4	6	15	20	8800	0.22	200
HFI-060303-2N4□	2.4	C,S	4	6	15	20	8300	0.24	200
HFI-060303-2N7□	2.7	C,S	5	6	16	20	7700	0.25	200
HFI-060303-3N0□	3.0	C,S	5	6	16	20	7200	0.28	180
HFI-060303-3N3□	3.3	C,S,K	5	6	16	20	6700	0.30	180
HFI-060303-3N6□	3.6	C,S,K	5	6	16	20	6400	0.30	170
HFI-060303-3N9□	3.9	C,S,K	5	7	16	20	6000	0.30	170
HFI-060303-4N3□	4.3	C,S,K	5	7	16	20	5700	0.40	150
HFI-060303-4N7□	4.7	C,S,K	5	7	16	20	5300	0.40	150
HFI-060303-5N1□	5.1	C,S,K	5	7	16	20	5000	0.40	150
HFI-060303-5N6□	5.6	C,S,K	5	7	16	20	4200	0.40	150
HFI-060303-6N2□	6.2	G,J,K	5	7	16	20	3800	0.44	150
HFI-060303-6N8□	6.8	G,J,K	5	7	16	20	3500	0.50	150
HFI-060303-7N5□	7.5	G,J,K	5	7	15	20	3300	0.53	150
HFI-060303-8N2□	8.2	G,J,K	5	7	15	20	3200	0.55	150
HFI-060303-9N1□	9.1	G,J,K	5	6	15	20	3000	0.62	150
HFI-060303-10N□	10	G,J,K	5	7	15	19	2800	0.65	150
HFI-060303-12N□	12	G,J,K	5	7	14	18	2400	0.70	100
HFI-060303-15N□	15	G,J,K	5	7	14	18	2200	0.80	100
HFI-060303-18N□	18	G,J,K	5	7	14	18	2100	0.90	100

PRODUCT SPECIFICATIONS

PART NUMBER	Inductance (nH) at 100 MHz	Tolerance	Q Min.	Q Typical			S.R.F.(MHz) Min.	R _{DC} (Ω) Max.	Rated Current (mA) Max.
			100 MHz	100 MHz	500 MHz	800 MHz			
HFI-060303-22N□	2.2	G,J,K	5	7	14	18	1800	1.20	100
HFI-060303-27N□	27	G,J,K	4	6	14	16	1800	1.80	50
HFI-060303-33N□	33	G,J,K	4	6	12	14	1700	2.10	50
HFI-060303-39N□	39	G,J,K	4	6	12	14	1500	2.40	50
HFI-060303-47N□	47	G,J,K	4	6	11	13	1300	2.80	50

TYPICAL ELECTRICAL CHARACTERISTIC CURVES




■ PRODUCT SPECIFICATIONS

PART NUMBER	INDUCTANCE (nH) AT 100 MHz	Q Min.	Q Typical	S.R.F.(MHz) Min.	R _{DC} (Ω) Max.	I _{DC} (mA) Max.						
		100MHz	800 MHz									
HFI-100505-1N0□	1.0	8	43	10000	0.12	300						
HFI-100505-1N1□	1.1				0.13							
HFI-100505-1N2□	1.2						0.14					
HFI-100505-1N3□	1.3							0.16				
HFI-100505-1N5□	1.5		41	6000					0.17			
HFI-100505-1N6□	1.6											
HFI-100505-1N8□	1.8											
HFI-100505-2N0□	2.0				36		0.19					
HFI-100505-2N2□	2.2		5000	0.22								
HFI-100505-2N4□	2.4							38	4000	0.24		
HFI-100505-2N7□	2.7										37	0.27
HFI-100505-3N0□	3.0				32		3900					
HFI-100505-3N3□	3.3		34	3700								
HFI-100505-3N6□	3.6							37	3500	0.37		
HFI-100505-3N9□	3.9										31	3400
HFI-100505-4N3□	4.3				35		3200					
HFI-100505-4N7□	4.7		26	1100								
HFI-100505-5N1□	5.1							23	900	1.30		
HFI-100505-5N6□	5.6										28	1400
HFI-100505-6N2□	6.2				30		2000					
HFI-100505-6N8□	6.8		34	3700								
HFI-100505-7N5□	7.5							37	3500	0.37		
HFI-100505-8N2□	8.2										31	3200
HFI-100505-9N1□	9.1				26		1200					
HFI-100505-10N□	10.0		24	1100								
HFI-100505-12N□	12.0							23	900	1.30		
HFI-100505-15N□	15.0										28	1400
HFI-100505-18N□	18.0				30		2000					
HFI-100505-22N□	22.0		34	3700		0.35						
HFI-100505-27N□	27.0							37	3500	0.37		
HFI-100505-33N□	33.0										31	3200
HFI-100505-39N□	39.0				26		1200					
HFI-100505-47N□	47.0		24	1100		1.20						
								23	900	1.30		
		28									1400	0.90
					30		2000					
			34	3700		0.35						
								37	3500	0.37		
		31									3200	0.42
					26		1200					
			24	1100		1.20						
								23	900	1.30		
		28									1400	0.90
					30		2000					
			34	3700		0.35						
								37	3500	0.37		
		31									3200	0.42
					26		1200					
			24	1100		1.20						
								23	900	1.30		
		28									1400	0.90
					30		2000					
			34	3700		0.35						
								37	3500	0.37		
		31									3200	0.42
					26		1200					
			24	1100		1.20						
								23	900	1.30		
		28									1400	0.90
					30		2000					
			34	3700		0.35						
								37	3500	0.37		
		31									3200	0.42
					26		1200					
			24	1100		1.20						
								23	900	1.30		
		28									1400	0.90
					30		2000					
			34	3700		0.35						
								37	3500	0.37		
		31									3200	0.42
					26		1200					
			24	1100		1.20						
								23	900	1.30		
		28									1400	0.90
					30		2000					
			34	3700		0.35						
								37	3500	0.37		
		31									3200	0.42
					26		1200					
			24	1100		1.20						
								23	900	1.30		
		28									1400	0.90
					30		2000					
			34	3700		0.35						
								37	3500	0.37		
		31									3200	0.42
					26		1200					
			24	1100		1.20						
								23	900	1.30		
		28									1400	0.90
					30		2000					
			34	3700		0.35						
								37	3500	0.37		
		31									3200	0.42
					26		1200					
			24	1100		1.20						
								23	900	1.30		
		28									1400	0.90
					30		2000					
			34	3700		0.35						
								37	3500	0.37		
		31									3200	0.42
					26		1200					
			24	1100		1.20						
								23	900	1.30		
		28									1400	0.90
					30		2000					
			34	3700		0.35						
								37	3500	0.37		
		31									3200	0.42
					26		1200					
			24	1100		1.20						
								23	900	1.30		
		28									1400	0.90
					30		2000					
			34	3700		0.35						
								37	3500	0.37		
		31									3200	0.42
					26		1200					
			24	1100		1.20						
								23	900	1.30		
		28									1400	0.90
					30		2000					
			34	3700		0.35						
								37	3500	0.37		
		31									3200	0.42
					26		1200					
			24	1100		1.20						
								23	900	1.30		
		28									1400	0.90
					30		2000					
			34	3700		0.35						
								37	3500	0.37		
		31									3200	0.42
					26		1200					
			24	1100		1.20						
								23	900	1.30		
		28									1400	0.90
					30		2000					
			34	3700		0.35						
								37	3500	0.37		
		31									3200	0.42
					26		1200					
			24	1100		1.20						
								23	900	1.30		
		28									1400	0.90
					30		2000					
			34	3700		0.35						
								37	3500	0.37		
		31									3200	0.42
					26		1200					
			24	1100		1.20						
								23	900	1.30		
		28									1400	0.90
					30		2000					
			34	3700		0.35						
								37	3500	0.37		
		31									3200	0.42
					26		1200					
			24	1100		1.20						
								23	900	1.30		
		28									1400	0.90
					30		2000					
			34	3700		0.35						
								37	3500	0.37		
		31									3200	0.42
					26		1200					
			24	1100		1.20						
								23	900	1.30		
		28									1400	0.90
					30		2000					
			34	3700		0.35						
								37	3500	0.37		
		31									3200	0.42
					26		1200					
			24	1100		1.20						
								23	900	1.30		
		28									1400	0.90
					30		2000					
			34	3700		0.35						
								37	3500	0.37		
		31									3200	0.42
					26		1200					
			24	1100		1.20						
								23	900	1.30		
		28									1400	0.90
					30		2000					
			34	3700		0.35						
								37	3500	0.37		
		31									3200	0.42
					26		1200					
			24	1100		1.20						
								23	900	1.30		
		28									1400	0.90
					30		2000					
			34	3700		0.35						
								37	3500	0.37		
		31									3200	0.42
					26		1200					
			24	1100		1.20						
								23	900	1.30		
		28									1400	0.90
					30		2000					
			34	3700		0.35						
								37	3500	0.37		
		31									3200	0.42
					26		1200					
			24	1100		1.20						
								23	900	1.30		
		28									1400	0.90
					30		2000					
			34	3700		0.35						
								37	3500	0.37		
		31									3200	0.42
					26		1200					
			24	1100		1.20						
								23	900	1.30		
		28									1400	0.90
					30		2000					
			34	3700		0.35						
								37	3500	0.37		
		31									3200	0.42
					26		1200					
			24	1100		1.20						
								23	900	1.30		
		28									1400	0.90
					30		2000					
			34	3700		0.35						
								37	3500	0.37		
		31									3200	0.42
					26		1200					
			24	1100		1.20						
								23	900	1.30		
		28									1400	0.90
					30		2000					
			34	3700		0.35						
								37	3500	0.37		
		31									3200	0.42
					26		1200					
			24	1100		1.20						
								23	900	1.30		
		28									1400	0.90
					30		2000					
			34	3700		0.35						
								37	3500	0.37		
		31									3200	0.42
					26		1200					
			24	1100		1.20						
								23	900	1.30		
		28									1400	0.90
					30		2000					
			34	3700		0.35						
								37	3500	0.37		
		31									3200	0.42
					26		1200					
			24	1100		1.20						

PRODUCT SPECIFICATIONS

PART NUMBER	Inductance (nH) at 100 MHz	Q Min.	Q Typical	S.R.F.(MHz) Min.	R _{DC} (Ω) Max.	Rated Current (mA) Max.
		100 MHz	800 MHz			
HFI-100505-56N□	56.0	8	21	750	1.40	200
HFI-100505-68N□	68.0		19			180
HFI-100505-82N□	82.0		16	600	1.60	150
HFI-100505-R10□	100.0		-			100
HFI-100505-R12□	120.0		-			

TYPICAL ELECTRICAL CHARACTERISTIC CURVES




■ PRODUCT SPECIFICATIONS


PART NUMBER	INDUCTANCE (nH) AT 100 MHz	Q Min.	Q Typical	S.R.F.(MHz) Min.	R _{DC} (Ω) Max.	I _{DC} (mA) Max.
		100MHz	800 MHz			
HFI-160808-1N0□	1.0	8	47	6000	0.10	1000
HFI-160808-1N2□	1.2					
HFI-160808-1N5□	1.5					
HFI-160808-1N8□	1.8					
HFI-160808-2N2□	2.2	10	49	4000	0.13	600
HFI-160808-2N7□	2.7		48			
HFI-160808-3N3□	3.3		51			
HFI-160808-3N9□	3.9		48			
HFI-160808-4N7□	4.7	12	46	3500	0.20	500
HFI-160808-5N6□	5.6		48			
HFI-160808-6N8□	6.8		50			
HFI-160808-8N2□	8.2		47			
HFI-160808-10N□	10.0	12	47	3200	0.23	400
HFI-160808-12N□	12.0		45			
HFI-160808-15N□	15.0		48			
HFI-160808-18N□	18.0		47			
HFI-160808-22N□	22.0	12	49	1600	0.25	300
HFI-160808-27N□	27.0		47			
HFI-160808-33N□	33.0		46			
HFI-160808-39N□	39.0		39			
HFI-160808-47N□	47.0	*8	37	900	0.28	200
HFI-160808-56N□	56.0		36			
HFI-160808-68N□	68.0		29			
HFI-160808-82N□	82.0		16			
HFI-160808-R10□	100.0	*8	17	500	1.0	100
HFI-160808-R12□	120.0 at 50MHz		-			
HFI-160808-R15□	150.0 at 50MHz		-			
HFI-160808-R18□	180.0 at 50MHz		-			
HFI-160808-R22□	220.0 at 50MHz	*8	-	400	1.20	50
HFI-160808-R27□	270.0 at 50MHz		-			

■ TYPICAL ELECTRICAL CHARACTERISTIC CURVES


Inductance vs. Freq. Characteristics



Q vs. Freq. Characteristics



Impedance vs. Freq. Characteristics




■ PRODUCT SPECIFICATIONS


PART NUMBER	INDUCTANCE (nH) AT 100 MHz	Q Min.	Q Typical	S.R.F.(MHz) Min.	R _{DC} (Ω) Max.	I _{DC} (mA) Max.
		100MHz *50MHz	800 MHz			
HFI-201209-1N5□	1.5	10	61	4000	0.10	300
HFI-201209-1N8□	1.8		55			
HFI-201209-2N2□	2.2		53			
HFI-201209-2N7□	2.7	12	56	3500	0.13	
HFI-201209-3N3□	3.3		47			
HFI-201209-3N9□	3.9		54			
HFI-201209-4N7□	4.7	15	55	3200	0.20	
HFI-201209-5N6□	5.6		60	2800	0.23	
HFI-201209-6N8□	6.8		63	2400	0.25	
HFI-201209-8N2□	8.2		60	2100	0.28	
HFI-201209-10N□	10.0			1900	0.30	
HFI-201209-12N□	12.0			1600	0.35	
HFI-201209-15N□	15.0		63	1500	0.40	
HFI-201209-18N□	18.0	18	60	1400	0.45	
HFI-201209-22N□	22.0		58	1300	0.50	
HFI-201209-27N□	27.0		55	1200	0.55	
HFI-201209-33N□	33.0		47	1000	0.60	
HFI-201209-39N□	39.0		43	900	0.65	
HFI-201209-47N□	47.0		39	800	0.70	
HFI-201209-56N□	56.0		30	700	0.75	
HFI-201209-68N□	68.0		-	600	0.80	
HFI-201209-82N□	82.0	*13	-	500	0.90	
HFI-201209-R10□	100.0		-		0.95	
HFI-201209-R12□	120.0 at 50 MHz		-		1.00	
HFI-201209-R15□	150.0 at 50 MHz	*12	-	350	1.10	
HFI-201209-R18□	180.0at 50 MHz		-		1.20	
HFI-201209-R22□	220.0 at 50 MHz		*10	-	300	
HFI-201209-R27□	270.0 at 50 MHz	-		1.40		
HFI-201209-R33□	330.0 at 50 MHz	*10		-	250	
HFI-201209-R39□	390.0 at 50 MHz		-	1.50		
HFI-201209-R47□	470.0 at 50 MHz			-	200	

■ TYPICAL ELECTRICAL CHARACTERISTIC CURVES

Inductance vs. Freq. Characteristics



Q vs. Freq. Characteristics



Impedance vs. Freq. Characteristics

