


Ceramic Composition 10% Tolerance






Series	Watts max.*	Resistance min. max.		Dimensions (in. / mm)			Joules max.**	Max Working volts	Qty. per reel
				Length L ±.039 (±1.0)	Length C max.	Diameter D ±.039 (±1.0)			
OX	1	3.3	100K	0.65 / 16.5	0.748 / 19.0	0.217 / 5.5	50	300	1000
OY	2	3.3	1M	0.748 / 19.0	0.886 / 22.5	0.276 / 7.0	80	400	500

* at 70°C. **For a single impulse.

The OX/OY Series of fixed ceramic resistors are ideal for circuitry associated with surges, high peak power or high energy. They offer enhanced performance in high voltage power supplies, R-C snubber circuits, and inrush limiters. The OX/OY resistors can often replace carbon composition resistors which can be difficult to source.

RESISTANCE TO PULSE



14KV and 20KV values used in circuit as shown; full voltage not applied directly to resistor.

FEATURES

- Replaces 1 and 2 watt carbon composition resistors
- Meets high energy density demands
- High peak power
- 10% Tolerance

SPECIFICATIONS

Material

Terminals: Pb Free Solder-coated
axial

Coating: UL-94 V0 approved silicone

Derating: Linear from 100% @ +70°C to 0% @ +200°C

Operating Temp. Range: -40°C
to +220°C


Electrical

Tolerance: $\pm 10\%$ standard

Power Rating: Based on 70°C free air rating.

Temperature Coefficient:
-1300 ±300ppm/°C.

REEL DIMENSIONS




PERFORMANCE CHARACTERISTICS

Test	0X	0Y
Max Working Voltage	300V	400V
Dielectric Strength	500V	700V
Max Overload Voltage	600V	800V
Max Pulse Voltage ¹	14KV	20KV
Pulse Tolerance, 100 pulses	1240V @ 52μF, 40J/ 35 sec.	1640V @ 52μF, 70J/35 sec.

Test	Condition	Maximum ΔR
Life Test	MIL-STD-202, Method 108	$\pm 5\%$
Short Time Overload	2x rated V, 5 sec ON @ 70°C	$\pm(2\% + 0.05\text{ohm})$
Resistance to Pulse ¹ 20,000 cycles	see circuit for test conditions	$\pm 5\%$
Thermal Shock	MIL-STD-202, Method 107	$\pm(2\% \pm 0.05 \text{ ohm})$
Moisture Resistance	1000 hrs @ 40°C, 90 - 95% RH	$\pm 5\%$

¹See figures, left

ORDERING INFORMATION



Check product availability at www.ohmite.com

STANDARD PART NUMBERS FOR OX/OY SERIES

Ohmic value	Part No.		Wattage		Ohmic value	Part No.		Wattage		Ohmic value	Part No.		Wattage		Ohmic value	Part No.		Wattage		Ohmic value	Part No.		Wattage									
	Prefix Suffix	▶ ▼	1 OX	2 OY		Part No.	Prefix Suffix	▶ ▼	1 OX		2 OY	Part No.	Prefix Suffix	▶ ▼		1 OX	2 OY	Part No.	Prefix Suffix		▶ ▼	1 OX	2 OY	Part No.	Prefix Suffix	▶ ▼	1 OX	2 OY				
3.3	—33GKE	✓	✓		27	—270KE	✓	✓		220	—221KE	✓	✓	✓		1800	—182KE	✓	✓	✓		15000	—153KE	✓	✓	✓		120000	—124KE	✓	✓	
3.9	—39GKE	✓	✓	✓	33	—330KE	✓	✓	✓	270	—271KE	✓	✓	✓		2200	—222KE	✓	✓	✓		18000	—183KE	✓	✓	✓		150000	—154KE	✓	✓	
4.7	—47GKE	✓	✓	✓	39	—390KE	✓	✓	✓	330	—331KE	✓	✓	✓		2700	—272KE	✓	✓	✓		22000	—223KE	✓	✓	✓		180000	—184KE	✓	✓	✓
5.6	—56GKE	✓	✓	✓	47	—470KE	✓	✓	✓	390	—391KE	✓	✓	✓		3300	—332KE	✓	✓	✓		27000	—273KE	✓	✓	✓		220000	—224KE	✓	✓	✓
6.8	—68GKE	✓	✓	✓	56	—560KE	✓	✓	✓	470	—471KE	✓	✓	✓		3900	—392KE	✓	✓	✓		33000	—333KE	✓	✓	✓		270000	—274KE	✓	✓	✓
8.2	—82GKE	✓	✓	✓	68	—680KE	✓	✓	✓	560	—561KE	✓	✓	✓		4700	—472KE	✓	✓	✓		39000	—393KE	✓	✓	✓		330000	—334KE	✓	✓	✓
10	—100KE	✓	✓	✓	82	—820KE	✓	✓	✓	680	—681KE	✓	✓	✓		5600	—562KE	✓	✓	✓		47000	—473KE	✓	✓	✓		390000	—394KE	✓	✓	✓
12	—120KE	✓	✓	✓	100	—101KE	✓	✓	✓	820	—821KE	✓	✓	✓		6800	—682KE	✓	✓	✓		56000	—563KE	✓	✓	✓		470000	—474KE	✓	✓	✓
15	—150KE	✓	✓	✓	120	—121KE	✓	✓	✓	1000	—102KE	✓	✓	✓		8200	—822KE	✓	✓	✓		68000	—683KE	✓	✓	✓		560000	—564KE	✓	✓	✓
18	—180KE	✓	✓	✓	150	—151KE	✓	✓	✓	1200	—122KE	✓	✓	✓		10000	—103KE	✓	✓	✓		82000	—823KE	✓	✓	✓		680000	—684KE	✓	✓	✓
22	—220KE	✓	✓	✓	180	—181KE	✓	✓	✓	1500	—152KE	✓	✓	✓		12000	—123KE	✓	✓	✓		100000	—104KE	✓	✓	✓		820000	—824KE	✓	✓	✓
																											1 MEG	—105KE	✓	✓	✓	