






REVISIONS				DOC. NO. SPC-F005, Total Pages: 2			
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD
129	A	RELEASED	DJC	3/11/98	JC	7/15/98	JMM



SPECIFICATIONS:

IMPEDANCE: 50 OHMS
WORKING VOLTAGE: 500 VRMS @ SEA LEVEL
FREQUENCY RANGE: 0-7 GHz
INSERTION LOSS: $\leq$ -.2 dB @ 3 GHz
VSWR MAX: 1.3:1 @ 3 GHz
FOR RG-58, 58A, 58C, 141, 141A, 400/U, BELDEN 8240, 8259, 8262, 9201, 9203, 9310, 9311,
COMM/SCOPE 0268 & CUSHCRAFT ULTRALINK TL92463E

ITEM	DESCRIPTION	QTY	MATERIAL	FINISH
9	FERRULE	1	BRASS	NICKEL
8	HEX NUT	1	BRASS	NICKEL
7	LOCK WASHER	1	BRASS	NICKEL
6	GASKET	1	S.L. RUBBER	RED
5	FERRULE STUD	1	BRASS	NICKEL
4	DIELECTRIC	1	DELRI	NONE
3	CONTACT	1	BRASS	GOLD
2	PRESS FIT BODY	1	BRASS	NICKEL
1	BODY	1	BRASS	NICKEL



SUGGESTED STRIPPING INSTRUCTIONS
SUGGESTED CRIMP DISS: .088 & .213

DISCLAIMER
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



SPC TECHNOLOGY

UNLESS OTHERWISE

SPECIFIED,

DIMENSIONS ARE

FOR REFERENCE

PURPOSES ONLY.

DRAWING TITLE:

TNC FEMALE CRIMP BULKHEAD

ELECTRONIC FILE

REV

SIZE DWG. NO.

1541

92N3387.DWG

A

DRAWN BY:

DANIEL CAREY

DATE:

3/11/98

CHECKED BY:

JOHN COLE

DATE:

7/15/98

APPROVED BY:

JEFF MCVICKER

DATE:

7/15/98

SCALE: NTS

U.O.M.: INCHES [mm]

SHEET: 1 OF 1