

ADN-C Series

120 - 960 Watts

Data Sheet

Total Power: 120-960 Watts
Input Voltage: 85-264 Vac,
 90-375 Vdc
of Outputs: Single

SPECIAL FEATURES

- Five year warranty
- High efficiency > 90% typical
- Full power at 60 °C
- Power Boost™
- Industrial grade design (metal case and mounting clip)
- MTBF > 450,000h demonstrated at 40 °C
- Active PFC > 0.92
- Adjustable output
- Overvoltage protection with autorecovery
- Continuous short circuit and overload protection
- SEMI F47 Sag Immunity
- Three status LEDs (Input, Output, Alarm)
- DC OK relay
- Parallel operation capability
- Screw terminal connections
- RoHS compliant
- 80 PLUS® compliant (ADN20-24-1PM-C model)
- No tools required for mounting

SAFETY

- UL508, cULus Listed
- UL 60950-1, cURus
- IEC60950-1
- Class I, Div 2 Hazardous Locations
- ATEX Certified on selected models
- IP20
- CE



Electrical Specifications

Input	
AC input range	Nominal: 100-240 Vac/115-230 Vac/85-264 Vac
DC input range	90-375 Vdc
Frequency	47-67 Hz, 400 Hz
Efficiency	> 90%
Inrush current (typical)	< 15A or < 60A depending on model
PFC	Active, better than 0.92
Output	
Nominal voltage	24 Vdc (22.5-28.5 Vdc Adj): ADN5-24-1PM-C & ADN10-24-1PM-C 24 Vdc (24-28 Vdc Adj): ADN20-24-1PM-C & ADN40-24-1PM-C
Initial voltage setting	24.5 V ± 1%
Hold-up time	> 20 ms at full load (100 Vac Input @ Tamb = +25 °C)
Voltage regulation	< ± 2% (combination line, load, time and temperature related changes)
Ripple	< 50 mVpp: ADN5-24-1PM-C & ADN10-24-1PM-C < 100 mVpp: ADN20-24-1PM-C & ADN40-24-1PM-C
Back EMF immunity	< 35 Vdc
Power Boost™	1.5 x Nominal current for 2 or 4 seconds depending on model
Short circuit current	1.5 x Nominal current at near zero volts at short circuit condition
Parallel operation	Switch selectable single unit or parallel unit operation. Units will not be damaged by parallel operation (regardless of switch position setting)
Output noise suppression	Radiated EMI values below EN61000-6-2
Overvoltage protection	> 30.5 Vdc but < 33 Vdc, auto recovery
Line and load regulation	< 0.5%
Time and temperature drift	< 1%

General Specifications

EMC emissions	EN61000-6-2:2001, EN61000-6-3:2001, Class B EN55011, EN55022 Radiated and Conducted including Annex. A, EN61000-3-2
EMC immunity	EN61000-6-1:2001, EN61000-6-2:2001, EN61000-4-2 Level 4, EN61000-4-3 Level 3, EN61000-4-6 Level 3, EN61000-4-4 Level 4 input and level 3 output. EN61000-4-5 Installation class 4, EN61000-4-11, IEC 61000-4-34 voltage dip immunity standard
Warranty	5 Years
General protection safety	Protected against continuous short-circuit, continuous overload, continuous open circuit. Protection Class 1 (IEC536), degree of protection IP20 (IEC60529) Safe low voltage: SELV (acc. IEC60950-1)
Status indicators	Visual: Three (3) status LEDs (Input, Output, Alarm) Relay: N.O. contact rated 200 mA/50 Vdc

LED Diagnostics

LED	OK	Loss of Ac	Low Ac	No Dc	High Load	Overload	Hot	Too Hot
Input	Green	---	Yellow	Green	Green	Green	Green	Green
Output	Green	---	Green	---	Yellow	Yellow	Green	---
Alarm	---	---	---	Red	Yellow	Red	Yellow	Yellow

Environmental Specifications

Storage temperature	-40 °C to + 85 °C; All models
Operating temperature	From -25 °C to 70 °C. Derate starting at 60 °C; All models Up to 50% load permissible with horizontal or on top mounting orientation

Other Features

External fusing	Not required. Unit provides internal fuse (not accessible)
Mounting orientation	Standard: Vertical, Optional: Horizontal or on Top Simple snap-on to DIN TS35/7.5 or TS35/15 rail system
Ventilation	Normal convection, No fan required
Cooling spacing	ADN5-24-1PM-C & ADN10-24-1PM-C: 15 mm in front, 25 mm above and below, 10 mm left and right ADN20-24-1PM-C: 15 mm in front, 40 mm above and below, 10 mm left and right ADN40-24-1PM-C: 15 mm in front, 25 mm above and below, 25 mm left and right
Connections	Input: Screw terminals, connector size range: 16-10 AWG (1.5 - 6 mm ²) for solid conductors Output: Two terminals per output, connector size range: 16-10 AWG (1.5 - 6 mm ²) for solid conductors One terminal per output for ADC40-24-1PM-C, connector size range: 7-6 AWG (10.6 - 13 mm ²) for solid conductors

Ordering Information

Model Number	Power	Input Voltage	Weight	Current	Case Type	MTBF
						Demonstrated at 40 °C
ADN5-24-1PM-C	120 W	85-264 Vac 90-375 Vdc*	1.10 lbs (500 g)	5 A @ 24 Vdc	Metal with mounting clip	550,000 hours
ADN10-24-1PM-C	240 W	85-264 Vac 90-375 Vdc*	1.98 lbs (900 g)	10 A @ 24 Vdc	Metal with mounting clip	550,000 hours
ADN20-24-1PM-C ¹	480 W	85-264 Vac 90-375 Vdc*	2.6 lbs (1200 g)	20 A @ 24 Vdc	Metal with mounting clip	450,000 hours
ADN40-24-1PM-C	960 W	100-240 Vac	6.0 lbs (2750 g)	40 A @ 24 Vdc	Metal with mounting clip	500,000 hours


*No UL listed for DC input

¹ 80 PLUS certified

Dimensions

	Height	Width	Depth
ADN5-24-1PM-C	4.85 in (123 mm)	1.97 in (50 mm)	4.37 (111 mm)
ADN10-24-1PM-C	4.85 in (123 mm)	2.36 in (60 mm)	4.37 (111 mm)
ADN20-24-1PM-C	4.85 in (123 mm)	3.42 in (87 mm)	4.96 in (126 mm)
ADN40-24-1PM-C	4.85 in (123 mm)	7.09 in (180 mm)	4.81 in (122 mm)

Mechanical Drawing



WORLDWIDE OFFICES

Americas

2900 S.Diablo Way
Tempe, AZ 85282
USA
+1 888 412 7832

Europe (UK)

Waterfront Business Park
Merry Hill, Dudley
West Midlands, DY5 1LX
United Kingdom
+44 (0) 1384 842 211

Asia (HK)

14/F, Lu Plaza
2 Wing Yip Street
Kwun Tong, Kowloon
Hong Kong
+852 2176 3333

ARTESYN
EMBEDDED TECHNOLOGIES

www.artesyn.com

Artesyn Embedded Technologies, Artesyn and the Artesyn Embedded Technologies logo are trademarks and service marks of Artesyn Embedded Technologies, Inc. All other names and logos referred to are trade names, trademarks, or registered trademarks of their respective owners. © 2017 Artesyn Embedded Technologies, Inc. All rights reserved. For full legal terms and conditions, please visit www.artesyn.com/legal.

For more information: www.artesyn.com/power
For support: productsupport.ep@artesyn.com

ADN-C Single-Phase DS 04Jan2017