



NOTES:


1. ALL DIMENSION IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. CONTACT RATING SWITCHING: 150mA, 250V AC/DC
350mA, 110V AC/DC
5. OPERATING FORCE: 425±100 CM/STANDARD
6. OPERATING TEMP: -30° to 85°C
7. CIRCUIT SP: 8 POSITIONS, 30° INDEX.
8. DIELECTRIC STRENGTH: 1000V RMS min.@Sea Level
9. DESIGNATE MAJOR DIMENSIONS
10. TIMING: BBM (Non-Shorting) Break Before Make.
11. HARDWARE SUPPLIED ON SWITCH— SEE BELOW
STOP RING, LOCKWASHER, & HEXNUT



CONTACT CONFIGURATION
(SEE NOTE 10)



TERMINATION DETAIL
SCALE 2X



E-SWITCH®																																		
<table border="1"> <tr> <td>B</td> <td>12821</td> <td>REV DESC PER NEW CATALOG</td> <td>2/28/03</td> <td>CJB</td> </tr> <tr> <td>A</td> <td>11512</td> <td>RELEASED FOR PRODUCTION</td> <td>5/30/01</td> <td>CJB</td> </tr> <tr> <td>REV.</td> <td>ECN No.</td> <td>DESCRIPTION</td> <td>DATE</td> <td>CHKD</td> </tr> </table> <table border="1"> <tr> <td colspan="5"> TITLE KC-18-A-(30.0mm) 01-N-L-S </td> </tr> <tr> <td>SCALE</td> <td>DATE</td> <td>DR</td> <td>DWG</td> <td>REV</td> </tr> <tr> <td>1.5:1</td> <td>5/30/01</td> <td>CJB</td> <td>G530160</td> <td>B</td> </tr> </table>					B	12821	REV DESC PER NEW CATALOG	2/28/03	CJB	A	11512	RELEASED FOR PRODUCTION	5/30/01	CJB	REV.	ECN No.	DESCRIPTION	DATE	CHKD	TITLE KC-18-A-(30.0mm) 01-N-L-S					SCALE	DATE	DR	DWG	REV	1.5:1	5/30/01	CJB	G530160	B
B	12821	REV DESC PER NEW CATALOG	2/28/03	CJB																														
A	11512	RELEASED FOR PRODUCTION	5/30/01	CJB																														
REV.	ECN No.	DESCRIPTION	DATE	CHKD																														
TITLE KC-18-A-(30.0mm) 01-N-L-S																																		
SCALE	DATE	DR	DWG	REV																														
1.5:1	5/30/01	CJB	G530160	B																														
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED																																		