


LOC	DIST	REVISIONS				
AJ	16	P	LTR	DESCRIPTION	DATE	DWN
			A	REV PER ECO 06-002539	07APR06	JH

D

C


B

A



DRILL HOLE TO RECEIVE
0.94±0.06 [.037±.002]
DIA PIN, 5 REQUIRED

SUGGESTED PCB CONFIGURATION



- 1 BERYLLIUM COPPER PER ASTM-B-197.
- 2 BRASS PER ASTM-B-16.
- 3 ZINC PER QQ-Z-363.
- 4 PTFE PER ASTM-D-1710.
- 5 SILVER PLATE PER QQ-S-365
2.54 μm [.000100] MINIMUM THICK.
- 6 TIN PLATE PER ASTM-B-545
2.54 μm [.000100] MINIMUM THICK.
- 7 NICKEL PLATE PER QQ-N-290
3.81 μm [.000150] MINIMUM THICK.
- 8. SEE INSTRUCTION SHEET 408-9889.

5413986-1
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. FERNANDEZ-DOCK5 22APR2005 CHK J. HAVENER 22APR2005		tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		JACK, 75 OHM, VERTICAL, PCB, BNC	
	0 PLC ± -		APVD J. LIPPERT 22APR2005		SIZE A2 CAGE CODE 00779 DRAWING NO C=5413986 RESTRICTED TO -		
	1 PLC ± -		PRODUCT SPEC 108-12078				
	2 PLC ± 0.20 [.008]		APPLICATION SPEC -				
	3 PLC ± -						
4 PLC ± -		ANGLES ± -					
MATERIAL SEE NOTES 1 - 4		FINISH SEE NOTES 5 - 7		WEIGHT -			
CUSTOMER DRAWING				SCALE 5:1		SHEET 1 of 1	
						REV A	