





1EN204-15B
M
DRAWING NUMBER
10
ISSUE
REVISIONS
A CO44351
PART 7
WJM
2 APR 79
CHECK
CE 3
1 APR 79
DRAWN
WJM
2 APR 79
FO-50378-003



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.				
CHARACTERISTICS		ELECTRICAL DATA		SCALE FULL
OPERATING FORCE ----- 6-12 LB		CONTACT ARRANGEMENT		DO NOT SCALE PRINT
FULL OVERTRAVEL FORCE ----- 30 LB MAX		S P D T (2)		
RELEASE FORCE ----- 4 LB MIN		28 VDC		UNLESS OTHERWISE NOTED DIMENSIONS ARE IN INCHES TOLERANCES ARE: ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES 1/2
PRETRAVEL ----- .040 MAX		LOAD	SEA LEVEL 50,000 FT.	
DIFFERENTIAL TRAVEL ----- .020 MAX		RES	4 4	
OVERTRAVEL ----- .250 MIN		IND	2 2	
		MOTOR	4	
				WEIGHT 11.0 OZ MAX

- NOTES
- 1 - CORROSION RESISTANT STEEL ENCLOSURE
 - 2 - SWITCH SEALED PER MIL-S-8805 SYMBOL 4
 - 3 - CIRCUIT DIAGRAM AND CATALOG LISTING ARE SHOWN ON NAMEPLATE
 - 4 - COINCIDENCE OF OPERATING AND RELEASING POINTS: .010 OF PLUNGER TRAVEL

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[1EN204-15B](#)