


Restricted to: General Release


USED ON

THIS DRAWING IS A CONTROLLED DOCUMENT
Rev 10
L28959



Left Side

Connector(s): MT-RJ (No Pins)
Mode: MM
Housing Color: Black
Geom. Spec: 115-1215



VIEW C-C
NOT TO SCALE

Fiber Path

Fiber A - - - - - B
Fiber B - - - - - A

Notes:

- 1 IL tested at 1300nm.
- 2 Product and Processing must meet requirements of Tyco Electronics Standard 230-702
- 3 Label 2 will not be present on any cable assembly less than 5 meters long.
- 4 Includes dust caps (not shown on print).

Right Side


Connector(s): LC-Duplex
Mode: MM
Housing Color: Beige
Geom. Spec: N/A

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT MAY NOT BE DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA 17105-3608.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

	B	Rev Per EC#	06-022379	9/27/2006	-	MK			
P	LTR	REVISION RECORD	DATE	DATE	DATE	DATE	DATE	DATE	DATE



Customer Print

DIN	Cable Assy Configurator	MATERIAL	HEAT TREAT
OK	Michael Kepko		
APVD	Michael Kepko		
NAME	FO C/A - 2 fiber, XG - 50/125, OFNR (Riser) jacket, MT-RJ (No Pins) to LC-Duplex		
SCALE	NTS	SIZE	A2
DRAWING NO	C- 6588719	SHEET	1 of 2
REV	B		

AMP Tyco Electronics, Inc.
Harrisburg, PA 17105-3608

THIS DRAWING IS A CONTROLLED DOCUMENT.

Restricted to: General Release

USED ON

Part #	L (meters)	L (feet)	MT-RJ (No Pins), Black		LC-Duplex, Beige	
			IL (dB)	RL (dB)	IL (dB)	RL (dB)
0-6588719-1	0.950 - 1.050	3.11 - 3.44	0.5	20	0.5	-
0-6588719-2	1.950 - 2.050	6.39 - 6.72	0.5	20	0.5	-
0-6588719-3	2.950 - 3.050	9.67 - 10.00	0.5	20	0.5	-
0-6588719-4	3.920 - 4.080	12.86 - 13.38	0.51	20	0.51	-
0-6588719-5	4.920 - 5.080	16.14 - 16.66	0.51	20	0.51	-
0-6588719-6	6.016 - 6.176	19.73 - 20.26	0.51	20	0.51	-
0-6588719-7	7.235 - 7.395	23.73 - 24.26	0.51	20	0.51	-
0-6588719-9	8.850 - 9.150	29.03 - 30.01	0.51	20	0.51	-
1-6588719-0	9.850 - 10.150	32.31 - 33.30	0.52	20	0.52	-
1-6588719-2	11.850 - 12.150	38.87 - 39.86	0.52	20	0.52	-
1-6588719-7	16.830 - 17.170	55.21 - 56.33	0.53	20	0.53	-
1-6588719-8	18.105 - 18.471	59.40 - 60.60	0.53	20	0.53	-
2-6588719-0	19.800 - 20.200	64.96 - 66.27	0.53	20	0.53	-
2-6588719-5	24.140 - 24.628	79.20 - 80.80	0.54	20	0.54	-
3-6588719-0	30.175 - 30.785	99.00 - 101.00	0.55	20	0.55	-

Qty	U of M	Description	Item No.
1	piece	HOUSING, CONN, MT-RJ,BLACK	1
1	piece	DUST COVER, MT-RJ	2
1	piece	SPRING, MT-RJ, 3.8 DESIGN	3
1	piece	PIN KEEPER, 3.8MM	4
1	piece	MT-RJ, SPRING PUSH, UNIVERSAL	5
1	piece	CRIMP EYELET, MT-RJ	6
2	piece	LC, SC, FC Straight Boot, Beige	7
1	piece	LC Duplex clip, black	8
2	piece	LC Connector Assy, MM	9
1	piece	MT-RJ FERRULE, THERMOPLAST,MM	10
AR	meter	2 fiber, XG-50/125, 1.8mm, Twinzip, Aqua, OFNR (Riser)	11
1	piece	MT-RJ TwinZip Bend Limiting Boot, Beige	12
2	piece	Eyelet/Shrink tube assembly - White	13
2	piece	Trace Label	14

Label 1

Per specification 107-1645-1



Trace # - Bar Code

Trace # - Human Readable

Part Number

Country of Origin

This label is used on all lengths on this drawing.

Label 2

Per specification 107-1645-1



Trace # - Bar Code

Trace # - Human Readable

Part Number

Country of Origin

This label is used on all lengths on this drawing.

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT MAY NOT BE DISCLOSED TO ANY OTHERS WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

	B	Rev Per EC#	06-022379	9/27/2006	-	MK	
P	LTR	REVISION RECORD		DATE	DIN	APVD	

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
meters		9 P.L.C.	± .
		1 P.L.C.	± .
		2 P.L.C.	± .
		3 P.L.C.	± .
		4 P.L.C.	± .

Customer Print

DIN Cable Assy Configurator		MATERIAL	HEAT TREAT	
CHK	Michael Kepko	-	-	
APVD	Michael Kepko	AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608		
NAME	FO C/A - 2 fiber, XG - 50/125, OFNR (Riser) jacket, MT-RJ (No Pins) to LC-Duplex			
SCALE	SIZE	DRAWING NO	SHEET	REV
NTS	A2	C- 6588719	2 of 2	B

8

7

6

5

4

3

2

1