

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20



BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REVISED PER 0G3B-0106-01	04SEP2001	EZ	DB
	D	REVISED PER 0G3B-0119-01	04SEP2001	EZ	DB



282842-2 AS SHOWN

- 1 MATERIALS AND FINISH
HOUSING: PA 6-6, UL 94-V0, COLOR GREEN.
CLAMP: BRASS, NICKEL PLATED.
TERMINAL: BRASS, TIN PLATED.
CLAMPING SCREW: M3, BRASS, NICKEL PLATED.



2 SUITABLE FOR 1,6-2,4mm. PCB THICKNESS.

3 WIRE SIZE RANGE
SOLID WIRE: 0,03-2,5mm² (13AWG)
STRANDED WIRE: 0,03-1,5mm² (15AWG)

4 RECOGNIZED UNDER THE COMPONENT PROGRAM OF
UNDERWRITERS LABORATORIES INC. FILE N° E60677.


5 IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY
WITH IEC 998-1/998-2-1.

6 NOT CUMULATIVE TOLERANCE.



90	13	1-282482-3
85	12	1-282842-2
80	11	1-282842-1
75	10	1-282842-0
70	9	282842-9
65	8	282842-8
60	7	282842-7
55	6	282842-6
45	5	282842-5
35	4	282842-4
25	3	282842-3
15	2	282842-2
DIM. A	N° OF POS.	PART NUMBER

RECOMMENDED PC BOARD LAYOUT



THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN 04SEP2001 E. ZANOLINI	Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm		CHK 04SEP2001 D. BIEVENOUR	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 04SEP2001 D. BIEVENOUR	TERMINAL BLOCK, PCB MOUNT SIDE ENTRY WIRE 10.00mm PITCH	
0 PLC ±-		PRODUCT SPEC	SIZE	
1 PLC ±.3		108-20166	CAGE CODE	
2 PLC ±.25		APPLICATION SPEC	DRAWING NO	
3 PLC ±-		114-20079	RESTRICTED TO	
4 PLC ±-		WEIGHT	A3 00779	
ANGLES ±2		CUSTOMER DRAWING	C=282842	
FINISH		SCALE 3:1	SHEET 1 OF 1	
1		REV D		