

# Navigation Switch Multidirectional

**multicomp**



## Specifications:

### Mechanical:

Operating Force	: 4-direction: 160gf
Center Push	: 320gf
Stroke	: 4-direction: 5° + 2.5° / -1.5° mm
Center Push	: 0.25+0.1/-0.2mm
Operating Temperature Range	: -25°C to +85°C

### Electrical:

Electrical Life	: 100,000 cycle.
Rating	: 50mA, 12V DC
Maximum Contact Resistance	: 100mΩ
Minimum Insulation Resistance	: 100MΩ at 100V DC
Dielectric Strength	: 250V AC/1 minute
Contact Arrangement	: 1 pole 1 throw

### Material:

Base	: Nylon high-temperature thermoplastic
Colour	: Black
Cover	: Nickel silver
Centre Stem	: Nylon high-temperature thermoplastic
5 Directions Colour	: Black
4 Directions Colour	: Brown
Four Way Stem	: Nylon high-temperature thermoplastic
Contact	: Stainless with silver cladding
Terminal	: Brass with silver plated

### Soldering Process:


Hand Soldering	: Use a soldering iron of 30W, controlled at 350°C approximately 5 seconds while applying
Reflow Soldering	: When applying reflow soldering, the peak temperature or the reflow over should be set to 260°C maximum

# Navigation Switch


## Multidirectional

**multicomp**

## Temperature Profile:



MCMT4



Dimensions : Millimetres

[www.element14.com](http://www.element14.com)  
[www.farnell.com](http://www.farnell.com)  
[www.newark.com](http://www.newark.com)


**multicomp**

# Navigation Switch

## Multidirectional

**multicomp**

MCMT5



Dimensions : Millimetres

## Part Number Table

Description	Part Number
Navigation Switch, 4 Way, SMD	MCMT4-F-V
Navigation Switch, 5 Way, SMD	MCMT5-F-V

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.

[www.element14.com](http://www.element14.com)  
[www.farnell.com](http://www.farnell.com)  
[www.newark.com](http://www.newark.com)

**multicomp**