



- NOTES:
1. MATERIAL:
HOUSING: POLYESTER(PBT), GLASS FILLED, UL94 V-0,
COLOR: BLACK
TERMINAL: PHOSPHOR BRONZE
 2. FINISH:
15 GOLD: 0.38 MICROMETERS/15 MICROINCHES MINIMUM GOLD IN
191 MICROMETERS/75 MICROINCHES MINIMUM TIN
OVER NICKEL UNDERPLATE OVERALL
 3. TO BE USED WITH 26 AWG STRANDED WIRE WITH (1.35)/.053
DIAMETER MAXIMUM INSULATION
 4. SEE TABLE FOR AVAILABLE CIRCUIT SIZES
 5. STANDARD PACKAGING PER PK-70873-0001. OPTIONAL PACKAGING
MAY BE AVAILABLE, REQUEST DRAWING PK-70400
 6. PARTS STACKABLE END TO END ON (2.54)/.100 CENTERS
 7. PRODUCT SPECIFICATION: PS-70400
 8. SEE DRAWING SDA-70400-**** (SHEET 3) FOR OPTIONAL
HOUSING DETAILS
 9. 4 CIRCUIT SHOWN. 3-25 CIRCUITS HAVE 2 RIBS
 10. TO MATE WITH MOLEX PART NUMBERS: A-70374-****,
A-70376-****, A-70390-****, A-70392-****,
A-70544-****, A-70554-****, A-70542-****,
A-70552-****, A-70546-****, A-70556-****,
 11. 2 CIRCUIT ASSEMBLIES SUPPLIED AS GROUPED PAIRS

OPTION C



I.D. SLOT CODE TO WIRE GAUGE CHART	
I.D. SLOT CODE	WIRE GAUGE
B	26 AWG.


PLATING CODE (STRIPE ON CARRIER STRIP)	
PLATING	COLOR
15 GOLD	YELLOW



SECTION C-C



PRE-LOADED
ASSEMBLY



FINAL
ASSEMBLY

WIRE (SEE NOTE 3)

REMOVE ENG NO. EC NO: UCP2011-110 DRWN:MS BARRA 2010/10/19 CHKD:J MORGAN 2010/10/19 APPR:SMILLER 2010/11/24	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION	
			mm	INCH	DRAWN BY MS BARRA	DATE 2010/10/19	TITLE ASSEMBLY, SL CONNECTOR SINGLE ROW 2.54/.100 GRID			
			4 PLACES ± ---	± ---	CHECKED BY WAZ	DATE 1984/10/10				
			3 PLACES ± ---	± .010	APPROVED BY SMILLER		DATE 2010/11/24		 MOLEX INCORPORATED	
			2 PLACES ± 0.25	± .014						
			1 PLACE ± 0.35	± ---	ANGULAR ±1/2°		MATERIAL NO. SEE TABLE		DOCUMENT NO. SDA-70400-0736-0759	SHEET NO. 1 OF 1
REV	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

CKT. SIZE	A	B	EDP. NO.
2	(2.54) .100	(5.05) .199	I4-56-3026
3	(5.08) .200	(7.59) .299	I4-56-3036
4	(7.62) .300	(10.13) .399	I4-56-3046
5	(10.16) .400	(12.67) .499	I4-56-3056
6	(12.70) .500	(15.21) .599	I4-56-3066
7	(15.24) .600	(17.75) .699	I4-56-3076
8	(17.78) .700	(20.29) .799	I4-56-3086
9	(20.32) .800	(22.83) .899	I4-56-3096
10	(22.86) .900	(25.37) .999	I4-56-3106
11	(25.54) 1.000	(27.91) 1.099	I4-56-3116
12	(27.94) 1.100	(30.45) 1.199	I4-56-3126
13	(30.48) 1.200	(32.99) 1.299	I4-56-3136
14	(33.02) 1.300	(35.53) 1.399	I4-56-3146
15	(35.56) 1.400	(38.07) 1.499	I4-56-3156
16	(38.01) 1.500	(40.61) 1.599	I4-56-3166
17	(40.64) 1.600	(43.15) 1.699	I4-56-3176
18	(43.18) 1.700	(45.69) 1.799	I4-56-3186
19	(45.72) 1.800	(48.23) 1.899	I4-56-3196
20	(48.26) 1.900	(50.77) 1.999	I4-56-3206
21	(50.80) 2.000	(53.31) 2.099	I4-56-3216
22	(53.34) 2.100	(55.85) 2.199	I4-56-3226
23	(55.88) 2.200	(58.39) 2.299	I4-56-3236
24	(58.42) 2.300	(60.93) 2.399	I4-56-3246
25	(60.96) 2.400	(63.47) 2.499	I4-56-3256