


[PRODUCTS](#)
[COMPANY](#)
[CONTACT US](#)
[SUPPORT](#)
[SITE MAP](#)
[PRODUCT SEARCH](#)

327-J/03


ARTICLE NUMBER e.g.20.874.002

[PRODUCTS](#)
[CROSS-REFERENCE](#)


TYPE Jumper Combs, Type 327-J

Inventory Check

Series	Download PDF	3D Model	Can plug with	How to order	Print
--------	--------------	----------	---------------	--------------	-------



RoHS WEEE Pb free surface compliant



Dimensions: mm (in.)

Length of Jumper (L)

L = (No. of Poles x Center to Center Spacing)

When locating connector, allow 0.5 mm clearance around it for process-induced variations.

Material

Jumper: copper alloy Insulation: PVC

Temperature limits:

Short Time: 149°C (300°F)**Continuous:** 93°C (200°F)**Low Limit:** -34°C (-30°F)**Comparative Tracking Index:** CTI≥600V**Oxygen Index Rating:** 39%

Description

Series 300-J jumper combs are designed for use with series 300 terminal strips, and allow electrical connection between adjacent poles. Jumper combs are secured in the terminal strip by the wire clamping screws, the exposed portion of the jumper is insulated to prevent accidental shock or short circuiting.

- For use with 326, 327 /-FU and HDS versions
- For electrical connection between adjacent poles

Technical Data

2 to 12 poles

[Top of page](#)

How to order

Item — Jumper Combs, Type 327-J

Ordering Note: Uninsulated jumpers and alternate insulation colors. Please consult factory.

☒ Request sample

☐ Request quote

Quantity 1

327-J/

POLES:
02 to 12
[Add to shopping cart](#)

2008, WECO Electrical Connectors Inc.

ISO 9001 registered quality management system