


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		C	REVISED PER 0G3B-0326-01	23JUL2001	EZ	DB
			D	REVISED EC 0G3B-0191-03	30APR2003	SW	CR

0.5
TYP

POLARIZATION KEY SLOT

INTERLOCKING
FEATURE

CLAMPING SCREW



282807-3 AS SHOWN

1

2

3

4

5

6

7

MATERIALS AND FINISH

HOUSING: PA 6-6, UL 94-V0, COLOR GREEN.

CLAMP: BRASS, NICKEL PLATED.

CONTACT SPRING: PHOSPHOR BRONZE, TIN PLATED.

CLAMPING SCREW: M3, BRASS, NICKEL PLATED.

END-TO-END STACKABLE W/INTERLOCK WITHOUT LOSS OF CENTERLINE SPACING.

WIRE SIZE RANGE

SOLID WIRE: 0,03-2,5mm (13 AWG).

STRANDED WIRE: 0,03-1,5mm (15 AWG).

RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC.FILE N° E60677

IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY WITH IEC 998-1/998-2-1.

NOT CUMULATIVE TOLERANCE.

CHARACTERS INK STAMPED WHITE.

A

15.5

RETENTION LATCH

MATING FACE

18.4

DETAIL Z

1

2

3

7

2.54 REF

2.54 REF

5.08±0.05
TYP

6

DETAIL Z

15.24

3

282807-5

20.32

4

282807-4

15.24

3

282807-3

10.16

2

282807-2

MARKING

L

NO OF POSN

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±.2

1 PLC ±.2

2 PLC ±.25

3 PLC ±.2

4 PLC ±.2

ANGLES ±2

FINISH

MATERIAL

-

DWN
E. ZANOLINI
23JUL2001

CHK
D. BIEVENOUR
23JUL2001

APVD
D. BIEVENOUR
23JUL2001

PRODUCT SPEC
108-20166

APPLICATION SPEC
114-20079

WEIGHT
-

CUSTOMER DRAWING

BUCHANAN

Tyco Electronics
Harrisburg, PA 17105-3608

NAME

TERMINAL BLOCK PLUG
STACKING W/INTERLOCK, 5.08mm PITCH

SIZE

A2

CAGE CODE

00779

DRAWING NO

C-282807

RESTRICTED TO

-

SCALE

3:1

SHEET

1

OF

1

REV

D