






MATERIALS	
BODY:	Phenolic, UL94 V-0
ACTUATOR:	Nickel Plated Brass
BUSHING:	Nickel Plated Brass
HOUSING:	Nickel Plated Steel
HARDWARE:	Nickel Plated Brass
SPACER PLATE:	Epoxy Board
SPRING:	Steel
ACTUATOR PLUNGER:	Phenolic, UL94 V-0
MOBILE CONTACT BAR:	Silver Plated Copper
CENTER PIVOT:	Silver Plated Copper
CONTACTS:	Silver Alloy Clad Copper
TERMINALS:	
SPECIFICATIONS	
FUNCTION:	1P2T (ON)–(OFF)–(ON)
RATINGS:	ANSI/UL1054 and CAN/CSA C22.2 129VAC [cURus] 20A 125VAC [cURus] 15A 277VAC [cURus] 1.5HP 125/277VAC [cURus]
CONTACT RESISTANCE:	Initial: 10mΩ Max. Insulation Resistance: 10MΩ Min.
DIELECTRIC STRENGTH:	1,500VAC for 1 Minute
OPERATING LIFE:	6,000 Cycles [cURus]
TEMPERATURE:	Operating: 0°C to 85°C [cURus]
APPROVALS:	  COMPLIANT



ACTUATOR	B	10/06/10	CAB
BODY	B	10/06/10	CAB
MATERIALS	B	10/06/09	CAB
SPECIFICATIONS	B	10/06/09	CAB
REFERENCE	REV.	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSMITTED

B	CORRECTED PANEL CUTOFF, SPECIFICATIONS, AND MATERIALS
A	INITIAL RELEASE
REV.	DESCRIPTION

19133	10/06/10	CAB
PCR00051	09/06/05	CAB
PCR	DATE	DRAWN BY

INCHES [MILLIMETERS]	
GENERAL TOLERANCES	
± 0.008 [± 0.2] / $\pm 1^\circ$	
SCALE	PROJECTION
DRAWING NOT TO SCALE	

DRAWING NUMBER		DATE	REVISION
34-ST14DD00		JUNE 10, 2010	B

