







FCIconnect.com

Copyright FCI



CABLE DIMENSIONS



NOTES:-

1. THE "LF" PRODUCTS MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
2. LEAD FREE OR RoHS DIRECTIVE LABELING TO BE PROVIDED AS PER GS-14-920 FOR RoHS COMPATIBLE VERSION.

Number of contacts	64	78.74	81.58	86.08	80.01	81.28	0.89
	60	73.66	76.50	81.00	74.93	76.20	0.89
	50	60.96	63.80	68.30	62.23	63.50	0.89
	40	48.26	51.10	55.60	49.53	50.80	0.89
Dimensions							

ORDERING INFORMATION

SERIES

NO.OF CONTACTS :-

40,50,60,64

3 - FEMALE WITH CENTRAL POLARISING

0 - WITHOUT STRAIN RELIEF CLAMP

1 - WITH STRAIN RELIEF CLAMP

TYPE OF TERMINATION

30 - INSULATION DISPLACEMENT 28 GAUGE

SPECIAL CODE

000 - TIN LEAD VERSION
E1LF - LEAD FREE VERSION

LONGITUDINAL PITCH
5 - 2.54 mm

PERFORMANCE CLASS

4 - DIN 41651 CLASS 3

5 - DIN 41651 CLASS 2

6 - DIN 41651 CLASS 1

8 - AS PER JSS 50810

INSULATOR MATERIAL

3 - PBT GREY

TECHNICAL SPECIFICATION

HOUSING MATERIAL : THERMOPLASTIC POLYESTER UL 94V0; GREY

CONTACT MATERIAL : COPPER ALLOY

PLATING : ACTIVE ZONE - GOLD OVER NICKEL

TERMINATION ZONE - SnPb OVER Ni FOR TIN LEAD VERSION.
- Sn (MATTE TIN) OVER Ni FOR LEAD FREE VERSION.

CURRENT RATING : 1.5A AT 20°C

INSULATION RESISTANCE AT 500Vdc : ≥5000 MΩ at 100V

CONTACT RESISTANCE : ≤20 mΩ

DIELECTRIC WITHSTANDING VOLTAGE : 1000 Vrms

OPERATING TEMPERATURE : -55°C TO +125°C

REFERENCE SPECIFICATION : IEC 603-13 / DIN 41651

mat'l. code				surface		tolerance		projection		product family									
-				ISO 1302		ISO 406		ISO 1101		8613									
litr				ecn no		dr		date		title									
A				-		YMP		1998-12-06		FEMALE CONNECTOR									
B				-		MINI		2002-04-22		FLAT CABLE 8613 SERIES									
C				I06-0066		MINI		2006-06-01		scale -									
D				I06-0173		MINI		2006-09-15		sheet 1 of 1									
										size									
										A3									
										type									
										Product Customer Drawing									
sheet				revision		D													
index				sheet		1													