

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

FCI

A






B

PRODUCT NO.
SEE TABLE

1 2

3

4



VIEW B
(CENTER PEG OMITTED FOR CLARITY)

mat'l. code SEE NOTES				tolerances unless otherwise specified				CUSTOMER COPY		A FCI www.fciconnect.com				
ltr	ecn no	dr	date	linear	.X ±.3				projection 	title RJ45 R/A 10 PORT GANG JACK FILTER ASSY 8 POS SHIELDED DIAMOND PEG				
A	V03-0446	LP	4/17/03		.XX ±.10									
B	M05-0066	MHT	4/7/05		.XXX ±.050									
				angles	0° ±2°					product family size	MOD JACK		code	
				dr	L.POTTEIGER	4/17/03		dwg no			213			
				engr	J.KONTOS	4/17/03								
				chr	J.KONTOS	4/17/03		scale 1:1	A	10027589		sheet		
				appd	J.KONTOS	4/17/03						1 of 4		
sheet index	revision sheet	B 1	A 2	B 3	A 4									

A

B

1 2

3

4

ACAD

PDM: Rev:B


STATUS: Released

cage code
22526


Printed: Aug 01, 2010

FCI

PRODUCT NO.
SEE TABLE




VIEW C-C



VIEW E


SCALE: 2/1

TYP FOR ALL GROUND SPRINGS



VIEW D

SCALE: 2/1

mat'l. code SEE NOTES				tolerances unless otherwise specified		CUSTOMER COPY	 www.fciconnect.com	
ltr	ecm no	dr	date	linear	angles			
A				.X ±.3		projection	title	
				.XX ±.10			RJ45 R/A 10 PORT GANG JACK FILTER ASSY	
				.XXX ±.050			8 POS SHIELDED DIAMOND PEG	
				0° ±2°		MM/INCH	product family	MOD JACK
				dr L.POTTEIGER 4/17/03		scale	size	dwg no
				enr J.KONTOS 4/17/03		1:1	A	10027589
				chr J.KONTOS 4/17/03				
				appd J.KONTOS 4/17/03				
sheet index	revision sheet							

cage code
22526

ACAD

PDM: Rev:B


STATUS: Released

Printed: Aug 01, 2010

PRODUCT NO.

10027589-X103LF


PLATING CODE X	PLATING ⑨
0	.76uM/30u" G.X.T.
1	.38uM/15u" GOLD
3	.76uM/30u" GOLD
5	1.27uM/50u" GOLD



RECOMMENDED PANEL OPENING

NOTES:

1. RECOMMENDED P.C.B. THICKNESS 1.60 [0.063].
2. HOUSING MATERIAL: HIGH TEMPERATURE THERMOPLASTIC, 94-V-0.
3. CONTACTS: PHOS BRONZE ALLOY, ϕ 0.460 [0.0181] ROUND WIRE, PLATING SEE TABLE.
4. SHIELD MAT'L: TIN PLATED BRASS ALLOY.
5. ALL DIMENSIONS IN MILLIMETERS/INCHES.
- ⑥ PART NUMBERS WITH LF IN THE END ARE LEAD FREE.
- ⑦ THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
8. THE HOUSING TEMPERATURE WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 15 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.5 MM MINIMUM THICK CIRCUIT BOARD. SEE APPLICATION NOTES/PROCEDURES IF THEY ARE AVAILABLE.
- ⑨ PLATING OPTION:
MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.

mat'l. code SEE NOTES				tolerances unless otherwise specified			CUSTOMER COPY		A FCI www.fciconnect.com					
ltr	ecn no	dr	date	linear	.X ±.3			projection 	title RJ45 R/A 10 PORT GANG JACK FILTER ASSY 8 POS SHIELDED DIAMOND PEG					
B					.XX ±.10									
					.XXX ±.050									
				angles	0° ±2°			MM/INCH	product family MOD JACK					code
				dr	L.POTTEIGER	4/17/03	size					213		
				enrg	J.KONTOS	4/17/03	dwg no							
				chr	J.KONTOS	4/17/03	scale					sheet		
				appd	J.KONTOS	4/17/03	1:1					3 of		
sheet index		revision												
sheet														

cage code
22526

