

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	0		D2	REVISED PER ECR-12-010267	05JUN12	JR	TM

- 1




0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN BRIGHT TIN-LEAD IN LOCALIZED TIN-LEAD PLATE AREA OVER 0.0013 [.000050] MIN NICKEL.
- 2

WIRE RANGE: 0.12 - 0.4MM² (26-22 AWG).
- 3


INSULATION RANGE: 1.19-1.75[.047-.069] DIA.
- 4

DIMENSIONS IN BRACKETS ARE IN INCHES.
- 5

0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN MATTE TIN IN LOCALIZED TIN PLATE AREA OVER 0.0013 [.000050] MIN NICKEL.




SECTION A-A
SCALE 20:1



SECTION B-B
SCALE 20:1

5	0.25[.010] BRASS	1-794218-0
1	0.25[.010] BRASS	794218-3
PRE-TIN	0.25[.010] BRASS	794218-1
FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN R. VESTAL 1-15-97		 TE Connectivity							
DIMENSIONS: mm [INCHES]			CHK R. SWING 1-15-97									
			TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME							
			0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.15 [.006] 4 PLC ± - ANGLES ± -		PIN, MINI UNIVERSAL MATE-N-LOK 2 -							
			FINISH		SIZE				CAGE CODE	DRAWING NO	RESTRICTED TO	
			SEE TABLE		A2				00779	C=794218	-	
MATERIAL SEE TABLE			WEIGHT -		CUSTOMER DRAWING					SCALE 10:1	SHEET 1 of 1	REV D2