





LOC		DIST		REVISIONS					
CM		O		P	LTR	DESCRIPTION	DATE	DWN	APVD
					E	ECO-06-013135	15JUN06	BSV	DC

- 1 MATERIAL:
HOUSING: NYLON, UL94V-0 (COLOR - NATURAL, COLOR OF PARTS MAY VARY).
CONTACTS - 0.25 THK COPPER ALLOY.
- 2 CONTACT FINISH: 0.003 MIN THK TIN-LEAD OVER 0.00127 MIN THK NICKEL OVER ENTIRE CONTACT.
- 3 CONTACT FINISH: 0.00076 MIN THK GOLD PLATE ON PIN MATING SURFACE, 0.003 MIN THK TIN-LEAD PLATE ON SOLDER TAIL, ALL OVER 0.00127 MIN THK NICKEL BASE PLATE.
- 4 SOLDER TAIL MEETS AMP SOLDERABILITY SPECIFICATION 109-11-2.
- 5 MATES WITH SIMILARLY PLATED AMP-DUAC™ POWER CONNECTOR RECEPTACLE HOUSINGS/SOCKET CONTACTS.
- 6 RIBS ON FOUR CORNERS OPTIONAL.
- 7 AMP LOGO AND MATERIAL ID MAY BE LOCATED ON EITHER LONG SIDE OF PART.
- 8 SIZE, SHAPE OR STYLE OF THIS FEATURE MAY VARY.
- 9 CONTACT FINISH: 0.003 MIN THK TIN OVER 0.00127 MIN THK NICKEL OVER ENTIRE CONTACT.
- 10 CONTACT FINISH: 0.00076 MIN THK GOLD PLATE ON PIN MATING SURFACE, 0.003 MIN THK TIN PLATE ON SOLDER TAIL, ALL OVER 0.00127 MIN THK NICKEL BASE PLATE.



RECOMMENDED MOUNTING HOLE PATTERN
FOR 1.78 MAX THICK P.C. BOARD
COMPONENT SIDE SHOWN



	1	10	1	1	1-794472-2			
	1	9	1	1	1-794472-1			
SUPERCEDED BY 1-794472-2	1	3	1	1	794472-2			
SUPERCEDED BY 1-794472-1	1	2	1	1	794472-1			
MATERIAL		FINISH		MATERIAL	COLOR	PART NO.		
CONTACT		HOUSING						
THIS DRAWING IS A CONTROLLED DOCUMENT.				OWN R. VESTAL CHK R. SWING C. CASH PRODUCT SPEC 108-1699 APPLICATION SPEC — WEIGHT —		OBJUN98 OBJUN98 OBJUN98 NAME ASSEMBLY, HEADER, VERTICAL, 24 POSITION, W/PEGS, W/DRAIN HOLES, 94V-0, AMP-DUAC		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± 0.2 2 PLC ± 0.13 3 PLC ± — 4 PLC ± — ANGLES ± 0'30"		Tyco Electronics Corporation Harrisburg, Pa 17105-3608				
MATERIAL SEE TABLE	FINISH SEE TABLE		SIZE A1			CAGE CODE 00779	DRAWING NO C=794472	RESTRICTED TO —
CUSTOMER DRAWING				SCALE 5:1	SHEET 1	OF 1	REV E	