





LOC	DIST	REVISIONS									
		DF	H0	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD	
						A	REDRAWN	PER DF-6290	TA	10-12-92	JW
						B	REV	PER 0600-1174-93	TA	12-6-93	JW
						C	REV	PER 0600-4864-95	CT	1-96	JW
						D	REV	PER 0600-5129-96	TA	4-15-96	DW



VIEW Z-Z



RECOMMENDED P.C. BOARD LAYOUT

- CONTACT FINISH: .000015 THK. GOLD IN THE CONTACT AREA. GOLD FLASH ON THE REMAINDER, ALL OVER .000050 THK. NICKEL.
- POST TO BE SOLDER DIPPED. CONN. MUST MEET REQUIREMENTS OF AMP SPEC 109-11-1.
- CONTACT MATERIAL: GILDING METAL.
- TOLERANCE NON CUMULATIVE.
- TAB-HOUSING MATERIAL: FLAME RETARDANT THERMOSET DIALLYL PHTHALATE. COLOR: GREEN
- CUT OUT FOR KEYING BOSS, LOCATED WHERE REQD. (OPTIONAL)
- AMP P/N & DATE CODE, MARKED WITH .062 ±.015 HIGH CHARACTERS, THIS APPROXIMATE AREA.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES [mm] TOLERANCES ON: 2 PLC DEC ± - 3 PLC DEC ±.005 [0.13] ANGLES ± -						PART NO	
DR T. ALEXANDER 10-9-92		CHK J. WARNER 10-12-92		APPD J. WARNER 10-12-92		NAME	
MATERIAL		APPD T. ALEXANDER 10-12-92		PRODUCT SPEC		ASSEMBLY, AMP BLADE, TAB HOUSING	
FINISH		APPLICATION SPEC		SIZE	CAGE CODE	DRAWING NO	
				D	00779	448274	
WEIGHT				SCALE	4:1	SHEET 1 OF 1	