




	10	9	8	7	6	5	4	3	2	1	
	PART NO.	ENG. NO.	CCTS.	TERMINAL	I.D. STRIPE	PLATING					
	38-00-2092	A-7720S-C 2J	2	41512-J(154)	BROWN	(0.00254)/.000100 MIN. TIN OVER (0.00127)/.000050 MIN. NICKEL					
F	↑ 2093	↑ C 3J	3	↑	↑						F
	2094	C 4J	4								
	2095	C 5J	5								
	2096	C 6J	6								
	2097	C 7J	7								
	2098	C 8J	8								
	2099	C 9J	9								
E	2100	C10J	10								E
	2101	C11J	11								
	2102	C12J	12								
	2103	C13J	13								
	2104	C14J	14								
	2105	C15J	15								
	2106	C16J	16								
D	2107	C17J	17								D
	2108	C18J	18								
	2109	C19J	19								
	2110	C20J	20								
	2111	C21J	21								
	2112	C22J	22								
C	2113	C23J	23								C
	2114	C24J	24								
	2115	C25J	25								
	2116	C26J	26								
	↓ 2117	↓ C27J	27	↓	↓						
	38-00-2118	A-7720S-C28J	28	41512-J(154)	BROWN						

NOTE: 18 - 28 CIRCUITS ARE NON-STANDARD.

CHANGE PLATING EC NO: UCP2011-1314 DRWN:WK/PER 2010/11/16 CHKD:JBELL APPR:FSM/TH 2011/03/09	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
	 	mm	INCH	DRAWN BY MCC	DATE 2/1/86	TITLE KK (2.54)/.100 INSULATION DISPLACEMENT CONNECTOR ASSEMBLY MOLEX INCORPORATED				
		4 PLACES	± ---	± ---	CHECKED BY D.MORIARTY					DATE 2/1/86
		3 PLACES	± ---	± ---	APPROVED BY J.DENNEHY					DATE 2/1/86
		2 PLACES	± ---	± ---	MATERIAL NO.					DOCUMENT NO.
1 PLACE	± ---	± ---	ANGULAR ± ---°		SEE CHART		SDA-7720S-*N*		SHEET NO. 3 OF 3	
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						