








P.C. MOUNTING

ISOMETRIC
SCALE 2 : 1

CIRCUIT: SPDT

O.P. (MM)	P.T. (MM)
10.8±0.8	2.00 MAX.

O.P. = OPERATING POINT
P.T. = PRE-TRAVEL



NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
- RATING: 0.1A @ 5 VDC
0.1A @ 125VAC UL
- OPERATING FORCE: 35 ± 10 gf
- OPERATING TEMP: -25°C TO 75°C
- ELECTRICAL LIFE: 10,000 CYCLES MIN.
- MECHANICAL LIFE: 1,000,000 CYCLES MIN.
- INSULATION RESISTANCE: 100 MEGA-OHMS MIN.
- DIELECTRIC STRENGTH: 1,500VAC - 1 MINUTE
- ▲ DENOTES CRITICAL PARAMETER.
- PACKAGED IN TRAYS, 120 PIECES PER TRAY.
- 2002/95/EC (ROHS) COMPLIANT



TITLE SS075Q102F035V2A

A	18331	RELEASE FOR PRODUCTION	11/25/08	BLR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE	DATE	DR	DWG	REV
4:1	11/25/2008	BLR	Q971024	A