


	10	9	8	7	6	5	4	3	2	1
	MATERIAL NUMBER	ENGINEERING NUMBER	WIRE SIZE AWG	INSULATION COLOR	SPLICE ID MIN	MWID	LENGTH "L" MAX			
F	192020271	A-945X	22-18	RED	.055/ 1.40	.147/3.74	1.070/27.18			
	192020272	B-931X	16-14	BLUE	.078/ 1.98	.185/4.70	1.070/27.18			
	192020273	C-946X	12-10	YELLOW	.124/ 3.15	.261/6.63	1.150/29.21			



- NOTES:
1. SPLICE MATERIAL: COPPER
 2. SPLICE FINISH: TIN
 3. INSULATION MATERIAL: NYLON 6/6
 4. MWID = MAXIMUM WIRE INSULATION DIAMETER
 4. ASSEMBLY IS ROHS COMPLIANT.

INITIAL RELEASE		EC NO: WNA2011-0271		2011/02/07		2011/02/08		2011/02/25		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE ---		DESIGN UNITS INCH		 THIRD ANGLE PROJECTION	
A		REV		DESCRIPTION		 =0  =0		mm		INCH		DRAWN BY		DATE		TITLE BUTT CONNECTOR, SEAMED NYLAKRIMP, 22-10 AWG EXPANDED FLARE					
								4 PLACES ± --- ± ---		ETHRODAHL		2011/02/07									
								3 PLACES ± --- ± .005		CHECKED BY		DATE									
								2 PLACES ± 0.13 ± .010		JMACNEIL		2011/02/08		MOLEX MOLEX INCORPORATED							
								1 PLACE ± 0.25 ± .020		APPROVED BY		DATE									
								JMACNEIL		2011/02/25		MATERIAL NO.		DOCUMENT NO.		SD-19202-010		SHEET NO. 1 OF 1			
														SEE CHART		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					