


-2		-1	U/M	DWG SIZE		PART NO		DESCRIPTION		ITEM NO					
				← REVISION OF EACH ASSY NO (WHEN BLANK, USE DWG REVISION)											
QTY REQD PER ASSY				PARTS LIST											
DIMENSIONS IN INCHES. DO NOT SCALE PRINT. TOLERANCES UNLESS OTHERWISE SPECIFIED: 2 PLC DEC ±.25 3 PLC DEC ± 4 PLC DEC ± ANGLES ± SURF TEXTURE: ✓				MATL		HT TR		FIN							
				-		-		-		-					
				DR B. HIGMAN		APP 08JAN02		08JAN02							
				T. ELBIN											
2 PLC DEC ±.25 3 PLC DEC ± 4 PLC DEC ± ANGLES ± SURF TEXTURE: ✓				CHK -		REL -				AMP Incorporated Harrisburg, PA 17105-3608					
NAME								END FEED HDM APPLICATOR				MACHINE REF MINI APPL			
SCALE -						DWG NO		1385364				SHEET 1 OF 1		REV A	
REMOVE BURRS, BREAK SHARP EDGES R.015 MAX				CUSTOMER AND ASSEMBLY DRAWING								RESTRICTED TO			
CAGE CODE 00779															



		A	REVISED
P	F	LTR	REVISION RECORD

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1385364-1](#)