

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,19

© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC

DIST

CE

16

P

LTR

DESCRIPTION

DATE

DWN

APVD

E

REVISED PER 0A00-0067-00

08FEB2001

TA

SB

1

COLOR LISTED IS AFTER CURE.

OBSOLETE	MANUFACTURING AND FIELD USE	ALL	15MIN 100C	2 HR	AMBER	25 2GR PKS	250	501195-7
OBSOLETE	FIELD USE OR WHEN A FAST CURE AT ROOM TEMP REQUIRED	FSMA	45MIN 25C	2 MIN	STRAW	25 2GR PKS	125	501195-6
OBSOLETE	FOR USE IN HIGH TEMP ENVIRONMENT	FSMA	15MIN 100C	40 MIN	AMBER	25 2GR PKS	250	501195-5
	MANUFACTURING AND FIELD USE	FSD, RSD, ST STYLE, FSMA	24HR 25C OR 2HR 65C	30 MIN	BLUE	25 2GR PKS	250	501195-4
OBSOLETE	FIELD USE OR WHEN A FAST CURE AT ROOM TEMP REQUIRED	FSMA	45MIN 25C	2 MIN	STRAW	10 2GR PKS	50	501195-3
OBSOLETE	FOR USE IN HIGH TEMP ENVIRONMENT	FSMA	15MIN 100C	40 MIN	AMBER	25 7GR PKS	500	501195-2
OBSOLETE	MANUFACTURING AND FIELD USE	FSD, RSD, ST STYLE, FSMA	24HR 25C OR 2HR 65C	30 MIN	BLUE	25 7GR PKS	500	501195-1
	APPLICATION	CONNECTOR TYPE	CURE TIME	POT LIFE	1 COLOR	NO. OF PACKS WT. PER PACK	APPROX # OF CONNECTORS PER BOX	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-
1 PLC ±-
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±-
FINISH -

MATERIAL

-

DWN S.URICH 30NOV95
CHK R.RENN 30NOV95
APVD N.MILLER 30NOV95
PRODUCT SPEC
APPLICATION SPEC
WEIGHT -

AMP Incorporated
Harrisburg, PA 17105-3608

ADHESIVE, EPOXY

SIZE A2
CAGE CODE 00779
DRAWING NO. C-501195

CUSTOMER DRAWING
SCALE 1:1
SHEET 1 OF 1
REV E

AMP 1471-9 REV 10/93

08-FEB-01 15:13:11 amp34874/home/amp34874/ednmod