

D

C

B

A

D

C

B

A

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		B	ECO-06-000585	10AUG06	BSV	MK

SPECIFICATIONS:

MATERIALS:
CASE: HIGH TEMPERATURE POLYESTER.
ACTUATOR BUTTON: POLYAMIDE, COLOR: SEE CHART BELOW.
MOVING CONTACT: COPPER ALLOY,GOLD OVER NICKEL PLATE.
FIXED CONTACT/TERMINAL: COPPER ALLOY. TIN/LEAD PLATE.
TERMINAL SEAL: EPOXY.

ELECTRICAL:
CONTACT RATING: 0.4 VA MAX. @ 20 VDC OR PEAK AC.
INITIAL CONTACT RESISTANCE: 20 MILLIOHMS MAX.
INSULATION RESISTANCE: 1.000 MEGOHMS @ 500 VDC MIN.
DIELECTRIC STRENGTH: 1.000 VOLTS RMS @ SEA LEVEL.
LIFE EXPECTANCY: 100.000 CYCLES.

MECHANICAL:
ACTUATION FORCE: 50 TO 400 GRAMS.
ACTUATION TRAVEL: .030°.


ENVIROMENTAL:
OPERATING TEMPERATURE: -22°F TO +149°F (-30°C TO +65°C)
STORAGE TEMPERATURE : -22°F TO +149°F (-30°C TO +65°C)

NOTES:

- INTERPRET DRAWING PER ANSI Y14.5M-1982.
- MOUNTING HARDWARE SUPPLIED: (1) LOCKWASHER
(1) HEX NUT.

TERMINALS CONNECTED WITH BUTTON IN POSITIONS SHOWN.		
MODEL NO.		
TPC21RG-PC (*)	2 TO 1 (MOM) 5 TO 4	2 TO 3 (MOM) 5 TO 6
TPC21RG-PC (*)	OFF	1 TO 3 (MOM) 4 TO 6
TPC11FG-PC (*)	2 TO 1	2 TO 3 (MOM)
TPC11CG-PC (*)	OFF	1 TO 3 (MOM)
NOTE: DESIGNATION NUMBERS ARE FOR REFERENE ONLY AND DO NOT APPEAR ON THE SWITCHES		

(*)	ACTUATOR BUTTON COLORS
(0)	BLACK
(2)	RED
(6)	BLUE



RECOMMENDED HOLE LAYOUT
TOLERANCE ±.002 UNLESS
OTHERWISE NOTED

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.KIRCORIAN	03OCT96	tyco Electronics		Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: INCHES		CHK —	—	NAME PUSHBUTTON SWITCH SP & DP PC (TPC11-PC & TPC21-PC)			
		APVD —	—				
		PRODUCT SPEC —					
		APPLICATION SPEC —					
MATERIAL SEE SPECIFICATIONS		FINISH SEE SPECIFICATIONS	WEIGHT —	SIZE A2	CAGE CODE 00779	DRAWING NO C-1437572-3	RESTRICTED TO —
CUSTOMER DRAWING			SCALE 4:1		SHEET 1 of 1		REV B