

Audio Connector, Socket, 6.3 mm, 2-pole, solder terminals for PCB, insulated



Description

- PCB Mounting:
Screw-on mounting, from rear-side
- Audio entrances and exits
- Data and Signal transfer
- Audio Plug: 2-pole, insulated, straight

References

Alternative: Housing shielded 4833.2220

Weblinks


pdf-datasheet, html-datasheet, General Product Information, RoHS, CHINA-RoHS, REACH, Mating Connectors, e-Shop, SCHURTER-Stock-Check, Distributor-Stock-Check

Technical Data


Diameter	6.3 mm
Number of Poles	2-pole
Ratings DC	1 A / 30VDC
Ratings AC	1 A / 30VAC
Dielectric Strength	500 VDC
Insulation Resistance	> 50 MΩ @ 500VDC

Allowable Operation Temp.	-20 °C to 70 °C
Terminal	PCB terminals silver plated
Mounting	Screw-on mounting wall thickness max. 3.6 mm
Housing	insulated
Style	straight
Lifetime	5000 Insertions

Dimensions



Diagrams



All Variants

Product group	Diameter [mm]	Number of Poles	Terminal	Order Number
Audio Plug/Sockets	6.3	2-pole	PCB terminals	4833.2230

Availability for all products can be searched real-time: <http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

Packaging unit 100 Pcs

Mating Inlets/Plugs

Category / Description

[Audio Plug/Sockets Overview complete](#)



4833, solder terminal, screened, 2-pole, Audio Plug/Sockets, 6.3 mm	4833.1200
4833, solder terminal, insulated, 2-pole, Audio Plug/Sockets, 6.3 mm	4833.1210
4833, solder terminal, insulated, 2-pole, Audio Plug/Sockets, 6.3 mm	4833.1220

[Audio Plug/Sockets further types to 4833 Audio-Stecker, D=6,3mm](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schurter:](#)

[4833.223](#)