

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [74059-1004](#)
Status: **Active**
Overview: [VHDM® Backplane Connector Systems](#)
Description: VHDM® Single-Ended Board-to-Board Backplane Header, 2.00mm Pitch, Vertical, 6-Rows, Guide Pin Signal Module, Shield End Version, Pin End Version, 60 Circuits, Pin Length 5.15mm. Series:74074 Enables designers to create custom loaded connectors utilizing standard pin lengths 4.25, 4.75, 5.15 and 6.25mm

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-74031-999 \(PDF\)](#)

Agency Certification

UL E29179

General

Product Family Backplane Connectors
Series [74059](#)
Application Backplane
Application Tooling Documents TM-622010999
Comments No Keying Position
Component Type PCB Header
Overview [VHDM® Backplane Connector Systems](#)
Product Name VHDM®
Style N/A
UPC 800753257887

Physical

Circuits (Loaded) 60
Circuits (maximum) 60
Color - Resin Black
Durability (mating cycles max) 200
First Mate / Last Break No
Flammability 94V-0
Guide to Mating Part Yes
Keying to Mating Part None
Material - Metal Beryllium Copper, High Performance Alloy (HPA), Stainless Steel

Material - Plating Mating Gold
Material - Plating Termination Matte Tin
Material - Resin High Temperature Thermoplastic
Net Weight 7.036/g
Number of Columns 10
Number of Pairs Open Pin Field
Number of Rows 6
Orientation Vertical
PC Tail Length 2.50mm
PCB Locator No
PCB Retention None
PCB Thickness - Recommended 1.80mm
Packaging Type Tube
Pitch - Mating Interface 2.00mm
Pitch - Termination Interface 1.00mm
Polarized to PCB Yes
Surface Mount Compatible (SMC) Yes
Temperature Range - Operating -55°C to +105°C




image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[74059Series](#)

Mates With
74030 VHDM® Board-to-Board
Daughtercard Receptacle

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.
Global

Description	Product #
6-Row Pin and Shield Repair Tool	0622015800
Insertion Module for Advanced Mate Signal Header, 6-Row by 10-Wide, 20.00mm	0622020203
Insertion Module for Advanced Mate Signal Header, 6-	0622020207

Termination Interface: Style	Through Hole - Compliant Pin	Row by 10-Wide, 20.00mm
Electrical		6-Row Shield 0622016000
Current - Maximum per Contact	2A	Extraction Tool
Data Rate	3.125 Gbps	Insertion Module 0622011101
Shield Type	Ground Plane Shield	for Advanced Mate
Shielded	Yes	Signal Header, 6-
Voltage - Maximum	120V AC (RMS)/DC	Row by 11-Wide, 20.00mm
Material Info		Signal Pin Inserter 0622015700
		Repair Tool
Reference - Drawing Numbers		
Product Specification	PS-74031-999	
Sales Drawing	SD-74059-002	
VHDM and Very High Density Metric are trademarks of Amphenol Corporation		

This document was generated on 12/09/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[74059-1004](#)