






Specification: (Ta=32°C)	Code:	Description:
Heat transfer, cold side:	A	Air
Heat transfer, warm side:	A	Air
Cascade:	-	
Cooling power: [W]	034	33 W at dT=0°C. Tolerance: ±10%.
Voltage, nominal: [VDC]	12	12 VDC.
TEM Voltage: [VDC]		Nominal: 12 VDC, Max: 15 VDC.
TEM Current: [A]		Nominal: 3.5 A, Initial: 4.0 A. All at dT=0°C. Tolerance: ±10%.
Fan(s), cold side:	2	MTBF: 50,000 hrs. L10 at 25°C. Nominal current: 0.24 A. Voltage: 12 VDC ±10%.
Fan(s), warm side:	2	MTBF: 50,000 hrs. L10 at 25°C. Nominal current: 0.25 A. Voltage: 12 VDC ±10%.
Temperature controller, sensor:	0	None.
Temperature control settings, trim options:	0	-
Additional controller information:		
Temperature control position:	0	-
Options:	0	-
Weight:		0.9 kg
Overheating thermostat:		None.
Operating temperature:		-10°C to +49°C at nominal voltage.
TE-Module(s) temperature specification:		Max. surface temperature: 80°C.
Enclosed:		-
Packing:		Individual cardboard box.

Mounting hole print: 102x82




Electrical connections:
TEM+: Orange
TEM-: White
FAN+: Purple
FAN-: Blue

Comments / deviations: Heat sinks, shrouds and, if applicable, D-plates in anodised aluminium.				General tolerances: SS-ISO 2768-1 c			
Designed by: Henrik Höjer	Approved by: Hans Lindberg	Release date: 20050304	Customer: Supercool AB		Project: HDPC		
		Title: TE ASSEMBLY 12 VDC AIR-AIR					
		Part nr: AA-034-12-22-00-00		Rev. nr: 0	Status: 0	Scale: 1:2	Size, sheet A3, 1(3)



Cold side

Warm side



Comments / deviations: Heat sinks, shrouds and, if applicable, D-plates in anodised aluminium.					General tolerances: SS-ISO 2768-1 c		
Designed by: Henrik Höjer	Approved by: Hans Lindberg		Release date: 20050304	Customer: Supercool AB		Project: HDPC	
 Supercool AB Box 27, S-40120 Göteborg, Sweden tfn: +46 31 420530, fax: +46 31 247909 e-mail: info@supercool.se Web: www.supercool.se			Title: TE ASSEMBLY 12 VDC AIR-AIR				
			Part nr: AA-034-12-22-00-00		Rev. nr: 0	Status: 0	Scale: 1:2