







Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.




title	4 LANE VERTICAL SMT HEADER	dwg no	10045646	Rev.	B
catalog no		CUSTOMER		sheet 2 of 3	



WITH PICK-UP CAP ATTACHED
SCALE 2:1

1. MATERIAL:
HOUSING: HIGH TEMPERATURE PLASTIC, BLACK COLOR, UL94V-0
CONTACT: COPPER ALLOY
HOLD DOWN: COPPER ALLOY
2. FINISH:
1.27um MIN NICKEL UNDERPLATE OVERALL,
1.91um MIN TIN (LEAD-FREE) ON SOLDER TAIL,
0.76um MIN GOLD IN CONTACT AREA
3. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
4. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A CONVECTED, INFRARED OR VAPOR PHASE REFLOW OVEN
5. CONTACT WIPE: 2.07 MIN FDR SIGNAL AND 2.52 MIN FDR GROUND



SCALE 2:1
RECOMMENDED PCB LAYOUT
(ALL TOLERANCES ARE ± 0.05)

4 LANE VERTICAL SMT HEADER	no 10045646	Rev	B
		CUSTOMER sheet 3 of 3	
catlog no			