


# Data sheet

2017-07-06  
Product version 00  
Document revision 1

**Order No.: 1861247**

**Type: FKCOR 2,5/ 3-ST-5,08**

**Plug component, Push-in spring connection**



The figure shows a 10-position version

## 1 Main features



- |                           |                           |                        |                     |
|---------------------------|---------------------------|------------------------|---------------------|
| • No. of pos.             | 3                         | • Nominal current      | 12 A                |
| • Conductor cross section | 2.5 mm <sup>2</sup>       | • Nominal voltage      | 320 V               |
| • Color                   | green                     | • Connection direction | 90 °                |
| • Pitch                   | 5.08 mm                   | • Type of packaging    | packed in cardboard |
| • Connection method       | Push-in spring connection |                        |                     |

## 2 Your advantages

- ✓ The conductor connection orthogonal to the direction of operation simplifies the cabling of DIN-rail-mountable devices
- ✓ Time saving push-in connection, tools not required
- ✓ Intuitive use through colour coded actuation lever
- ✓ Quick and convenient testing using integrated test option
- ✓ Can be combined with the MSTB 2',5 range



Make sure you always use the latest documentation.  
It can be downloaded at: [phoenixcontact.net/product/1861247](https://phoenixcontact.net/product/1861247)

**3 Table of contents**

|      |                                                              |    |
|------|--------------------------------------------------------------|----|
| 1    | Main features .....                                          | 1  |
| 2    | Your advantages .....                                        | 1  |
| 3    | Table of contents .....                                      | 2  |
| 4    | 3D model in PDF can be activated (Acrobat Reader only) ..... | 3  |
| 5    | item properties .....                                        | 4  |
| 5.1  | Connection capacity .....                                    | 4  |
| 5.2  | Specifications for ferrules .....                            | 4  |
| 5.3  | Material data .....                                          | 4  |
| 6    | Dimensions .....                                             | 4  |
| 6.1  | Dimensions for the product .....                             | 4  |
| 7    | Series drawing .....                                         | 6  |
| 8    | Packaging information .....                                  | 7  |
| 9    | Application .....                                            | 7  |
| 9.1  | Temperature limit values .....                               | 7  |
| 10   | Mechanical tests .....                                       | 8  |
| 10.1 | Termination and connection method .....                      | 8  |
| 10.2 | Pull-out test .....                                          | 8  |
| 11   | Electrical tests .....                                       | 9  |
| 11.1 | Electrical data .....                                        | 9  |
| 11.2 | Air and creepage distances .....                             | 9  |
| 12   | Current carrying capacity/derating curves .....              | 10 |
| 13   | Environmental and durability tests .....                     | 11 |
| 13.1 | Vibration test .....                                         | 11 |
| 14   | Classification for connectors .....                          | 11 |
| 15   | Approvals .....                                              | 11 |
| 16   | Commercial Data .....                                        | 12 |
| 17   | Accessories .....                                            | 12 |
| 18   | Combination tests .....                                      | 13 |

1861247 FKCOR 2,5/ 3-ST-5,08

#### 4 3D model in PDF can be activated (Acrobat Reader only)



**1861247 FKCOR 2,5/ 3-ST-5,08****5 item properties**

|                     |                           |
|---------------------|---------------------------|
| Order No.           | 1861247                   |
| Type                | FKCOR 2,5/ 3-ST-5,08      |
| Type of contact     | Female connector          |
| Range of articles   | FKCOR 2,5/...-ST          |
| Pitch               | 5.08 mm                   |
| Number of positions | 3                         |
| Connection method   | Push-in spring connection |

**5.1 Connection capacity**

|                                   |                                            |
|-----------------------------------|--------------------------------------------|
| Conductor cross section, solid    | 0.2 mm <sup>2</sup> to 2.5 mm <sup>2</sup> |
| Conductor cross section, flexible | 0.2 mm <sup>2</sup> to 2.5 mm <sup>2</sup> |
| Conductor cross section AWG/kcmil | 24 to 12                                   |
| Stripping length                  | 10 mm                                      |

**5.2 Specifications for ferrules**

|                                                              |                                                                                                                                                                                                                                                                                                                                                                                                                                        |
|--------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Ferrules without insulating collar, according to DIN 46228–1 | Cross section: 0.25 mm <sup>2</sup> ; Length: 7 mm<br>Cross section: 0.34 mm <sup>2</sup> ; Length: 7 mm<br>Cross section: 0.5 mm <sup>2</sup> ; Length: 8 mm ... 10 mm<br>Cross section: 0.75 mm <sup>2</sup> ; Length: 8 mm ... 10 mm<br>Cross section: 1 mm <sup>2</sup> ; Length: 8 mm ... 10 mm<br>Cross section: 1.5 mm <sup>2</sup> ; Length: 8 mm ... 10 mm<br>Cross section: 2.5 mm <sup>2</sup> ; Length: 8 mm ... 10 mm     |
| Ferrules with insulating collar, according to DIN 46228–4    | Cross section: 0.14 mm <sup>2</sup> ; Length: 8 mm<br>Cross section: 0.25 mm <sup>2</sup> ; Length: 8 mm ... 10 mm<br>Cross section: 0.34 mm <sup>2</sup> ; Length: 8 mm ... 10 mm<br>Cross section: 0.5 mm <sup>2</sup> ; Length: 8 mm ... 10 mm<br>Cross section: 0.75 mm <sup>2</sup> ; Length: 8 mm ... 10 mm<br>Cross section: 1.5 mm <sup>2</sup> ; Length: 8 mm ... 10 mm<br>Cross section: 2.5 mm <sup>2</sup> ; Length: 10 mm |

**5.3 Material data**

|                                        |                                                                         |     |
|----------------------------------------|-------------------------------------------------------------------------|-----|
| Material of metal parts                |                                                                         |     |
| Note                                   | WEEE/RoHS-compliant, whisker-free acc. to IEC 60068-2-82/JEDEC JESD 201 |     |
| Contact material                       | Cu alloy                                                                |     |
| Terminal point surface                 | Sn 4 µm ... 8 µm                                                        |     |
| Surface contact area                   | Sn 4 µm ... 8 µm                                                        |     |
| Surface characteristics                | hot-dip tin-plated                                                      |     |
| Insulating material data               | Housing                                                                 |     |
| Insulating material                    | PA                                                                      | PBT |
| CTI according to IEC 60112             | 600                                                                     | 275 |
| Flammability rating according to UL 94 | V0                                                                      | V0  |
| Color                                  | green (6021)                                                            |     |


**6 Dimensions****6.1 Dimensions for the product**

**1861247 FKCOR 2,5/ 3-ST-5,08**

Document revision 1

|              |          |
|--------------|----------|
| Length       | 23.7 mm  |
| Width        | 15.11 mm |
| Total height | 14.3 mm  |
| Dimension a  | 10.16 mm |

7 Series drawing



**1861247 FKCOR 2,5/ 3-ST-5,08****8 Packaging information**

|                    |                     |
|--------------------|---------------------|
| Type of packaging  | packed in cardboard |
| Pieces per package | 250                 |

**9 Application****9.1 Temperature limit values**

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| Ambient temperature (storage/transport) | -40 °C ... 70 °C                         |
| Ambient temperature (assembly)          | -5 °C ... 100 °C                         |
| Ambient temperature (operation)         | -40 °C (dependent on the derating curve) |

**1861247 FKCOR 2,5/ 3-ST-5,08****10 Mechanical tests****Mechanical test group A**

|                                     |                        |
|-------------------------------------|------------------------|
| Specification                       | IEC 61984:2008-10      |
| Visual test                         | Test passed            |
| Specification                       | IEC 60512-1-1:2002-02  |
| Dimensional test                    | Test passed            |
| Specification                       | IEC 60512-1-2:2002-02  |
| Resistance of marking               | Test passed            |
| Specification                       | IEC 60068-2-70:1995-12 |
| Insertion and withdrawal force      | Test passed            |
| Specification                       | IEC 60512-13-2:2006-02 |
| No. of cycles                       | 25                     |
| Insertion strength per pos. approx. | 8 N                    |
| Withdraw strength per pos. approx.  | 11 N                   |
| Polarization and coding             | Test passed            |
| Specification                       | IEC 60512-13-5:2006-02 |
| Test force                          | 20 N                   |
| Contact retention in insert         | Test passed            |
| Specification                       | IEC 60512-15-1:2008-05 |
| Test force per pos.                 | 20 N                   |

**10.1 Termination and connection method**

|                                            |                     |
|--------------------------------------------|---------------------|
| Specification                              | IEC 60999-1:1999-11 |
| Check for damage to conductor or loosening | Test passed         |

**10.2 Pull-out test****Termination and connection method: pull-out test**

|                                                                    |                                         |
|--------------------------------------------------------------------|-----------------------------------------|
| Specification                                                      | IEC 60999-1:1999-11                     |
| Result                                                             | Test passed                             |
| Conductor cross section/conductor type/tractive force actual value | 0.2 mm <sup>2</sup> / solid / > 10 N    |
| Conductor cross section/conductor type/tractive force actual value | 0.2 mm <sup>2</sup> / stranded / > 10 N |
| Conductor cross section/conductor type/tractive force actual value | 2.5 mm <sup>2</sup> / solid / > 50 N    |
| Conductor cross section/conductor type/tractive force actual value | 2.5 mm <sup>2</sup> / stranded / > 50 N |
| Conductor cross section/conductor type/tractive force actual value | AWG 12 / stranded / > 60 N              |

**1861247 FKCOR 2,5/ 3-ST-5,08****11 Electrical tests****11.1 Electrical data**

|                                         |                            |
|-----------------------------------------|----------------------------|
| Rated current / conductor cross section | 12 A / 2.5 mm <sup>2</sup> |
| Rated insulation voltage (III/2)        | 320 V                      |
| Rated surge voltage (III/2)             | 4 kV                       |
| Contact resistance                      | 1.3 mΩ                     |
| Degree of pollution                     | 2                          |

**11.2 Air and creepage distances**

|                                                                   |                     |       |        |
|-------------------------------------------------------------------|---------------------|-------|--------|
| Component                                                         | Plug component      |       |        |
| Specification                                                     | IEC 60664-1:2007-04 |       |        |
| Mains type                                                        | unearthed mains     |       |        |
| Insulating material group                                         |                     |       |        |
| Comparative tracking index (IEC 60112:2003-01)                    | CTI 600             |       |        |
| Rated insulation voltage                                          | 250 V               | 320 V | 630 V  |
| Rated surge voltage                                               | 4 kV                | 4 kV  | 4 kV   |
| Degree of pollution                                               | 3                   | 2     | 2      |
| Overvoltage category                                              | III                 | III   | II     |
| Minimum clearance case A (inhomogeneous field)                    | 3 mm                | 3 mm  | 3 mm   |
| Minimum value of the creepage path requirement in acc. with table | 3.2 mm              | 3 mm  | 3.2 mm |

**1861247 FKCOR 2,5/ 3-ST-5,08****12 Current carrying capacity/derating curves**

|                         |                                               |
|-------------------------|-----------------------------------------------|
| Specification           | IEC 61984:2008-10                             |
| Note                    | Representation based on IEC 60512-5-2:2002-02 |
| Reduction factor        | 0.8                                           |
| Number of positions     | See diagram                                   |
| Conductor cross section | 2.5 mm <sup>2</sup>                           |

**Type: FKCO(R/W) 2,5/...-ST-5,08-LR with MSTBA(R/W) 2,5/...-G-5,08-LR**

81345\_1000\_en

**Type: FKCO(R/W) 2,5/...-ST-5,08(-LR) with MSTBVA 2,5/...-ST-5,08(-LR)**

81491\_1000\_en

**1861247 FKCOR 2,5/ 3-ST-5,08****13 Environmental and durability tests****13.1 Vibration test**

|                        |                        |
|------------------------|------------------------|
| Specification          | IEC 60068-2-6:2007-12  |
| Result                 | Test passed            |
| Frequency              | 10 - 150 - 10 Hz       |
| Sweep speed            | 1 octave/min           |
| Amplitude              | 0.35 mm (10 - 60.1 Hz) |
| Acceleration           | 5 g (60.1 - 150 Hz)    |
| Test duration per axis | 2.5 h                  |
| Test directions        | X-, Y- and Z-axis      |

**14 Classification for connectors**

|                                   |                                              |
|-----------------------------------|----------------------------------------------|
| Specification                     | IEC 61984:2008-10                            |
| Main features                     | Connectors without switching capacity (COC)  |
| Construction form                 | Fixed connectors                             |
| Strain relief elements            | without strain relief                        |
| Connection method                 | Can be reconnected                           |
| Protection against electric shock | Not encapsulated - touch-proof when inserted |
| Protective conductor              | without PE                                   |
| Lock                              | no                                           |
| Connection method                 | Screwless terminal points                    |

**15 Approvals**

|                                                                                                      |       |       |  |  |
|------------------------------------------------------------------------------------------------------|-------|-------|--|--|
| cULus Recognized  |       |       |  |  |
| Use group                                                                                            | B     | D     |  |  |
| mm <sup>2</sup> /AWG/kcmil                                                                           | 26-12 | 26-12 |  |  |
| Voltage                                                                                              | 300 V | 300 V |  |  |
| Current                                                                                              | 12 A  | 10 A  |  |  |

**1861247 FKCOR 2,5/ 3-ST-5,08****16 Commercial Data**



|                    |                                                      |
|--------------------|------------------------------------------------------|
| Order No.          | 1861247                                              |
| Type               | FKCOR 2,5/ 3-ST-5,08                                 |
| Pieces per package | 250                                                  |
| Net weight         | 3.884 g                                              |
| GTIN               | 4055626125329                                        |
|                    | Information that applies locally, see link on page 1 |
| Country of origin  | Information that applies locally, see link on page 1 |

**17 Accessories**

| Description                                                                                                                                                      | Order No. | Type                     |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------|--------------------------|
| Coding profile, is inserted into the slot on the plug or inverted header, red insulating material                                                                | 1734634   | CP-MSTB                  |
|                                                                                                                                                                  | 0201744   | MPS-MT                   |
|                                                                                                                                                                  | 0201647   | RPS                      |
| Actuation tool, for ST terminal blocks, insulated, also suitable for use as a bladed screwdriver, size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip | 1205053   | SZS 0,6X3,5              |
|                                                                                                                                                                  | 0804293   | SK 5,08/3,8:FORTL.ZAHLEN |

## 1861247 FKCOR 2,5/ 3-ST-5,08

## 18 Combination tests

**FKCOR 2,5/..-ST****MSTBA 2,5/..-G-LR****MSTBVA 2,5/..-G-LR**

Specification

IEC 61984

IEC 61984

**Mechanical tests (A)**

Insertion/withdrawal force per position

approx. 8 N / 11 N

approx. 10 N / 12 N

Polarization when inserted  
Requirement > 20 N

Test passed

Test passed

Contact holder in insert  
Requirements > 20 N

Test passed

Test passed

**Endurance tests (B)**Contact resistance  $R_1$ 

1.3 mΩ

2.5 mΩ

Insertion/withdrawal cycles

25

25

Contact resistance  $R_2$ 

1.3 mΩ

2.4 mΩ

Rated impulse voltage at sea level  
Voltage waveform  $\geq (1.2/50 \mu s)$ 

4.8 kV

4.8 kV

Power-frequency withstand voltage  
Voltage waveform  $\geq (50/60 \text{ Hz})$ 

2.21 kV

2.21 kV

Insulation resistance  
Requirements > 5 MΩ

&gt; 1.5 TΩ

&gt; 1 TΩ

**Thermal tests (C)**

Tested number of positions

24

24

Tested conductor cross section

2.5 mm<sup>2</sup>2.5 mm<sup>2</sup>

Test current

12 A

12 A

Upper limiting temperature  
Requirements < 100°C

Test passed

Test passed

**Climatic tests (D)**

Test sequence 1: low temperature storage

-40 °C/2 h

-40 °C/2 h

Test sequence 2: heat storage

100 °C/168 h

100 °C/168 h

Test sequence 3: noxious gas storage  
(ISO 6988)0.2 dm<sup>3</sup> SO<sub>2</sub> on 300 dm<sup>3</sup>/  
40 °C/1 cycle0.2 dm<sup>3</sup> SO<sub>2</sub> on 300 dm<sup>3</sup>/  
40 °C/1 cycleRated impulse voltage at sea level  
Voltage waveform  $\geq (1.2/50 \mu s)$ 

4.8 kV

4.8 kV

Power-frequency withstand voltage  
Voltage waveform  $\geq (50/60 \text{ Hz})$ 

2.21 kV

2.21 kV

**Environmental and endurance tests (E)**

Specification

IEC 61984:2008-10

IEC 61984:2008-10

Degree of protection

Finger safety with IP20  
test fingerFinger safety with IP20  
test finger