






$$F_{XX^{*1}}P0G_{Y^{*2}}$$

e.g. F09P0G1

*1) xx No. of contacts 09, 15, 25 or 37

*2) y for performance classes 1, 2 or 3
(contact cycle for G1/G2/G3 = 500/200/50)

xx	A [mm]	B [mm]	C [mm]
09	30.8	16.9	25
15	39.1	25.2	33.3
25	53	38.9	47.04
37	69.3	55.3	63.5

② RoHS compliant

②	3	xx	Signal contact	P0 / Brass	AWG 20 / G1/G2/G3
	2	1	Shell	Steel	tin plated
	1	1	Insulator	PBT (-55°C - +125°C)	white
	No.	St.	Part	Type Description/Material	Surface plating/Colour/Class

				Measurement without tolerance occ. to ISO 2768-m	SCALE 2:1	TITLE D-Sub Miniature Connector			
				NAME / DATE					
			DRAWN	Denzinger 14-10-2002					
			CHECKED	ffloßmann 24-08-2006					
						DWG.NO.	FxxP0Gy	REV.	
2	24-08-2006	21889							2
1									
REV.	DATE	CH.-NO.	ORIGINAL: DIN A3-DRAWING AS A FILE			REPLACEMENT FOR:	PAGES 1		

COMMENT:
ALL RIGHTS ARE RESERVED BY US FOR THIS DRAWING. WITHOUT OUR PRIOR CONSENT,
IT MAY NEITHER BE DUPLICATED NOR MADE AVAILABLE TO A THIRD PARTY,
AND IT ALSO MAY NOT BE IMPROPERLY USED BY TE RECEIVER, OR A THIRD PARTY.