

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS					
P	LTR	DESCRIPTION			DATE	DWN	APVD
		REVISED PER ECO-10-013614			13OCT10	HMR	CR

MATERIAL:
HOUSING: THERMOPLASTIC, UL94V-0, BLACK.
TERMINALS: BRIGHT TIN OVER COPPER ALLOY.
SCREWS: #6-32 STEEL, ZINC PLATING W/ CLEAR CHROMATE.

ELECTRICAL:
RATED CURRENT UL/CSA:
CLASS C: 20A, 300V
CLASS D: 5A, 600V
WIRE RANGE: 12-22 AWG

MECHANICAL:
RECOMMENDED TORQUE: 7 IN-LB.
OPERATING TEMP.: 105°C MAX.

1 MARK WITH PERMANENT INK.



SEE FIGURE

SEE FIGURE
SEE FIGURE
SEE FIGURE
SEE FIGURE

9.000	9.314	23	JC6-P208-23	6-796985-5
8.625	8.939	22	JC6-P208-22-224	1776344-1
8.625	8.939	22	JC6-P208-22	6-796985-4
8.250	8.564	21	JC6-P208-21	6-796985-3
7.875	8.189	20	JC6-P208-20	6-796985-2
7.500	7.814	19	JC6-P208-19	6-796985-1
7.125	7.439	18	JC6-P208-18	2-796985-0
6.750	7.064	17	JC6-P208-17	6-796985-0
6.375	6.689	16	JC6-P208-16	5-796985-9
6.000	6.314	15	JC6-P208-15	1-796985-9
5.625	5.939	14	JC6-P208-14	5-796985-8
5.250	5.564	13	JC6-P208-13	5-796985-7
4.875	5.189	12	JC6-P208-12	5-796985-6
4.500	4.814	11	JC6-P208-11	5-796985-5
4.125	4.439	10	JC6-P208-10	5-796985-4
3.750	4.064	9	JC6-P208-09	4-1437665-6
3.375	3.689	8	JC6-P208-08	5-796985-3
3.000	3.314	7	JC6-P208-07	5-796985-2
2.625	2.939	6	JC6-P208-06	4-1437665-5
2.250	2.564	5	JC6-P208-05	4-1437665-4
1.875	2.189	4	JC6-P208-04-505	1776344-3
1.875	2.189	4	JC6-P208-04-504	1776344-2
1.875	2.189	4	JC6-P208-04-503	9-796985-7
1.875	2.189	4	JC6-P208-04-500	9-796985-6
1.875	2.189	4	JC6-P208-04	4-1437665-3
1.500	1.814	3	JC6-P208-03-172	1-796985-8
1.500	1.814	3	JC6-P208-03	4-1437665-2
1.125	1.439	2	JC6-P208-02	4-1437665-1
DIM. "B"	DIM. "A"	NO. OF POS.	CATALOG PART NO.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. SCHLEGEL 5/7/03	Tyco Electronics Corporation Harrisburg, PA 17105	
DIMENSIONS: INCHES		CHK S. YODER 5/7/03		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S. YODER 5/7/03	NAME	
0 PLC ± - 1 PLC ± - 2 PLC ± .01 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC	JC6-P208-XX ASSEMBLY	
MATERIAL		FINISH	SIZE	RESTRICTED TO
-		-	A3 00779 C-4-1437665-1	-
CUSTOMER DRAWING			SCALE NTS	SHEET 1 OF 2
			REV D	

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

BY TYCO ELECTRONICS CORPORATION.





LOC

FT




DIST

0




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—






9-796985-7




1776344-2




9-796985-6



1776344-3



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. SCHLEGEL 5/7/03		 Tyco Electronics Corporation Harrisburg, PA 17105				
		CHK S. YODER 5/7/03						
		APVD S. YODER 5/7/03						
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± .01 3 PLC ± - 4 PLC ± - ANGLES ± -		NAME				
				JC6-P208-XX ASSEMBLY				
				SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
				A3 00779		C-4-1437665-1		—
				CUSTOMER DRAWING		SCALE NTS	SHEET 2 OF 2	REV D
MATERIAL —		FINISH —		PRODUCT SPEC —				
				APPLICATION SPEC —				
				WEIGHT —				