






SEE SHEET 2 FOR HOLE PATTERN



3.56[.140]	5	1-5145165-2
3.17[.125]	4	5145165-8
2.54[.100]	3	5145165-4
2.54[.100]	4	5145165-2
2.54[.100]	5	5145165-1
W	FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
AL FRANTUM
CHK
AL FRANTUM
APVD

04 FEB 05
04 FEB 05
-

DIMENSIONS:

mm

0 PLC ± -
1 PLC ± -
2 PLC ± 0.25 [.01]
3 PLC ± 0.13 [.005]
4 PLC ± - ± 2°
ANGLES

MATERIAL

FINISH

PRODUCT SPEC

108-14034

APPLICATION SPEC

114-26012

WEIGHT

-

CUSTOMER DRAWING

NAME

CONNECTOR ASSEMBLY,
92 DUAL POSITION, .050 SERIES,
STANDARD EDGE

SIZE

A1

CAGE CODE

00779

DRAWING NO

5145165

RESTRICTED TO

-

SCALE

4:1

SHEET

1

OF


2

REV

C1


TE Connectivity

TE



RECOMMENDED CONNECTOR MOUNTING HOLE PATTERN
(CONNECTOR SIDE SHOWN)

- 1
- HOUSING: HIGH TEMPERATURE THERMOPLASTIC.
COLOR - NATURAL
- 2
- CONTACT: PHOSPHOR BRONZE.
- 3
- CONTACT FINISH: 0.00127[.000050] MIN NICKEL ALL OVER.
GOLD FLASH OVER NICKEL IN CONTACT AREA.
0.00254[.000100] MIN MATTE TIN OVER NICKEL ON SOLDER TAILS.
- 4
- CONTACT FINISH: 0.00127[.000050] MIN NICKEL ALL OVER.
0.00038[.000015] GOLD OVER NICKEL IN CONTACT AREA.
0.00254[.000100] MIN MATTE TIN OVER NICKEL ON SOLDER TAILS.
- 5
- CONTACT FINISH: 0.00127[.000050] MIN NICKEL ALL OVER.
0.00076[.000030] GOLD OVER NICKEL IN CONTACT AREA.
0.00254[.000100] MIN MATTE TIN OVER NICKEL ON SOLDER TAILS.
- 6
- DISTANCE FROM CONTACT POINT TO BOTTOM OF CARD SLOT.
- 7
- AMP PART NUMBER, DATE CODE AND CSA LOGO MARKED IN
APPROXIMATE LOCATION SHOWN.
- 8
- CORED OR SOLID SIDE WALLS ARE AT DISCRETION OF
AMP INCORPORATED.



RECOMMENDED MATING BOARD EDGE CONFIGURATION