

## AC Line Rated Ceramic Disc Capacitors Class X1, 400 V<sub>AC</sub>/Class Y4, 125 V<sub>AC</sub>



### FEATURES

- Worldwide safety agency recognition  
Underwriters laboratories - UL 1414  
Canadian standards association - CSA 22.2  
European EN132400 to IEC 60384-14 2<sup>nd</sup> edition
- Complete range of capacitance values
- Radial leads
- Material categorization: For definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)


**RoHS  
COMPLIANT**

### APPLICATIONS

- Required in AC power supply and filter applications
- Specific industry requirements

### DESIGN

The capacitors consist of a ceramic disc of which both sides are silver-plated. Connection leads are made of tinned copper having a diameter of 0.032" (0.81 mm) or 0.025" (0.64 mm). The capacitors may be supplied with radial kinked or straight leads having a lead spacing of 0.375" (9.5 mm) or 0.250" (6.4 mm). The standard tolerance is  $\pm 20\%$ . Coating is made of flame retardant epoxy resin in accordance with "UL 94 V-0".

### CAPACITANCE RANGE

1.0 nF to 0.050  $\mu$ F

### RATED VOLTAGE

IEC 60384-14.2:	(Y4): 125 V <sub>AC</sub> , 50 Hz
IEC 60384-14.2:	(X1): 400 V <sub>AC</sub> , 50 Hz
UL 1414:	250 V <sub>AC</sub> , 60 Hz
CSA 22.2 No.1:	125 V <sub>AC</sub> /250 V <sub>AC</sub> , 60 Hz

### DIELECTRIC STRENGTH BETWEEN LEADS

Component test:  
2000 V<sub>AC</sub>, 50 Hz, 2 s

As repeated test admissible only once with:  
1800 V<sub>AC</sub>, 50 Hz, 2 s

Random sampling test (destructive test):  
2000 V<sub>AC</sub>, 50 Hz, 60 s

### DIELECTRIC STRENGTH OF BODY INSULATION

2300 V<sub>AC</sub>, 50 Hz, 60 s (destructive test)

### QUICK REFERENCE DATA

DESCRIPTION	VALUE		
Ceramic Class	2		
Ceramic Dielectric	Y5V		
Voltage (V <sub>AC</sub> )	125	250	400
Min. Capacitance (pF)	1000		
Max. Capacitance (pF)	50 000		
Mounting	Through hole		

### INSULATION RESISTANCE

Min. 1000  $\Omega$ F

### TOLERANCE ON CAPACITANCE

 $\pm 20\%$ 

### DISSIPATION FACTOR

2.0 % max. at 1 kHz; 1 V

### CERAMIC DIELECTRIC

Y5V (Class 2)

### CATEGORY TEMPERATURE RANGE


- 25 °C to + 125 °C

### CLIMATIC CATEGORY ACC. TO EN60068-1

25/125/21

### OPERATING TEMPERATURE RANGE

- 30 °C to + 125 °C

**DIMENSIONS** in inches (millimeters)


LO' = 0.132" (3.4 mm) typ.

**ORDERING INFORMATION, CERAMIC X1/Y4 CAPACITORS 125L**








C (pF)	TOL. (%)	D <sub>max.</sub> DIAMETER INCH (mm)	T <sub>max.</sub> THICKNESS INCH (mm)	WIRE SIZE		LS LEAD SPACE INCH (mm)	ORDERING CODE
				AWG	INCH (mm)		
<b>Y5V</b>							
1000	± 20 %	0.330 (8.4)	0.195 (5.0)	20	0.032 (0.81)	0.250 (6.4)	125LD10-R
1500		0.330 (8.4)	0.195 (5.0)				125LD15-R
2000		0.330 (8.4)	0.188 (4.8)				125LD20-R
2200		0.330 (8.4)	0.182 (4.7)				125LD22-R
3300		0.365 (9.3)	0.195 (5.0)				125LD33-R
4700		0.400 (10.2)	0.185 (4.7)				125LD47-R
5000		0.430 (11.0)	0.195 (5.0)				125LD50-R
6800		0.490 (12.5)	0.198 (5.1)				125LD68-R
8200		0.530 (13.5)	0.193 (5.0)			0.375 (9.5)	125LD82-R
0.010 µF		0.560 (14.3)	0.195 (5.0)				125LS10-R
0.015 µF		0.720 (18.3)	0.205 (5.3)				125LS15-R
0.018 µF		0.790 (20.1)	0.205 (5.3)				125LS18-R
0.020 µF		0.720 (18.3)	0.250 (6.4)	22	0.025 (0.64)		125LS20-R
0.022 µF		0.790 (20.1)	0.192 (4.9)	20	0.032 (0.81)		125LS22-R
0.030 µF		0.720 (18.3)	0.240 (6.1)	22	0.025 (0.64)		125LS30-R
0.050 µF		0.925 (23.5)	0.275 (7.0)	22	0.025 (0.64)		125LS50-R

**Notes**

- Alternate lead spacings of 7.5 mm and 10 mm are available bulk or tape and reel on request.
- European required minimum lead clearance (prevents use of inside crimp) 0.118" (3 mm)

**TAPE AND REEL OPTIONS**

To specify tape and reel, add two letter suffix to the ordering code (for details of the packaging code see general section of the catalog)

**LEAKAGE CURRENT VS. VOLTAGE (TYPICAL)**

**INSERTION LOSS VS. FREQUENCY (TYPICAL)**


**APPROVALS**

IEC 60384 - 14/2<sup>nd</sup> Issue (1993) incl. Am.1 (1995) - Safety Tests  
 EN132400 (1994) - Safety Tests

That approval together with CB Test Certificate substitutes the national approval of the following nations:

Belgium	France	Italy	Austria	China	Japan	Spain
Denmark	Greece	Luxembourg	Portugal	Singapore	Poland	United Kingdom
Germany	Ireland	Netherlands	Sweden	Slovenia	Hungaria	Czech Republic
Finland	Iceland	Norway	Switzerland	Korea	Israel	

X1 Capacitor: CB-Test Certificate: DE 1-19447 1000 pF to 0.05 µF 400 V<sub>AC</sub>

Y4 Capacitor: CB-Test Certificate: DE 1-19447 1000 pF to 0.05 µF 125 V<sub>AC</sub>


**UNDERWRITERS LABORATORIES INC.**

**UL 1414** Line-by-pass component Agency File/License E99264 1000 pF to 0.05 µF 250 V<sub>AC</sub>


**CANADIAN STANDARDS ASSOCIATION**

**CSA C22.2 No. 1** Isolation component Agency File/License LR 62016 1000 pF to 0.05 µF 250 V<sub>AC</sub>


**Notes**

UL1414 Across-The-Line, Antenna Coupling, and Line-By-Pass Capacitors:

- Across-The-Line - a capacitor connected either across a supply circuit or between one side of a supply circuit and a conductive part that may be connected to earth ground.
- Antenna-Coupling - a capacitor connected from an antenna terminal to circuits within an appliance.
- Line-By-Pass - a capacitor connected between one side of a supply circuit and an accessible conductive part.

IEC 60384-14 Subclass Y Capacitors:


- A capacitor of a type suitable for use in situations where failure of the capacitor could lead to danger of electric shock.
- Class Y capacitors are divided into subclasses based on type of insulation bridged and voltage ranges.
- For definitions of basic, supplementary, double and reinforced insulation, see IEC publication 536.
- Subclass Y capacitors may be used in applications which require a subclass X rating.

IEC 60384-14 Subclass X Capacitors:

- A capacitor of a type suitable for use in situations where failure of the capacitor in situations where failure of the capacitor would not lead to danger of electric shock.
- Class X capacitors are divided into subclasses according to the peak impulse test voltage superimposed on the main voltage.

**MARKING**

Sample



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

## Material Category Policy

**Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.**

**Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.**

**Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[125LD10](#) [125LD15](#) [125LD50](#) [125LD82](#) [125LD20](#) [125LD47](#) [125LD68](#) [125LD10-R](#) [125LS20-R](#) [125LS20JJ](#)  
[125LD33](#) [125LD22](#) [125LS10JJ](#) [125LD47QH](#) [125LD47UB](#) [125LS22BR](#) [125LD47-R](#) [125LS22-R](#) [125LS15-R](#)  
[125LS18-R](#) [125LS30](#) [125LS15](#) [125LS10](#) [125LS18](#) [125LS20](#) [125LS22](#) [125LS50](#) [125LD10QM](#) [125LS10QQ](#)  
[125LS10QF](#) [125LS50-R](#) [125LS10-R](#) [125LS30-R](#) [125LD50-R](#) [125LD68-R](#) [125LD20-R](#) [125LD22-R](#) [125LD33-R](#)  
[125LSD47](#) [125LD82-R](#) [125LD15-R](#) [125LS10QQ-R](#)