

UUR

Chip Type, High CV



For SMD




Smaller



Anti-Solvent
Feature


- Chip type, higher capacitance in larger case sizes.
- Designed for surface mounting on high density PC board.
- Applicable to automatic mounting machine fed with carrier tape.
- Compliant to the RoHS directive (2011/65/EU).




Specifications

Item	Performance Characteristics										
Category Temperature Range	-40 to +85°C										
Rated Voltage Range	4 to 100V										
Rated Capacitance Range	3.3 to 1500μF										
Capacitance Tolerance	±20% at 120Hz, 20°C										
Leakage Current	After 1 minute's application of rated voltage at 20°C, leakage current is not more than 0.03CV (μA) .										
Tangent of loss angle (tan δ)	Measurement frequency : 120Hz at 20°C										
	Rated voltage (V)	4	6.3	10	16	25	35	50	63	100	
	tan δ (MAX.)	0.35	0.28	0.24	0.20	0.16	0.14	0.12	0.12	0.12	
Stability at Low Temperature	Measurement frequency: 120Hz										
	Rated voltage (V)		4	6.3	10	16	25	35	50	63	100
	Impedance ratio	Z-25°C / Z+20°C	7	5	4	3	2	2	2	2	2
	ZT / Z20 (MAX.)	Z-40°C / Z+20°C	15	10	8	6	4	3	3	3	3
Endurance	The specifications listed at right shall be met when the capacitors are restored to 20°C after the rated voltage is applied for 2000 hours at 85°C.						Capacitance change		Within ±20% of the initial capacitance value		
							tan δ		200% or less than the initial specified value		
							Leakage current		Less than or equal to the initial specified value		
Shelf Life	After storing the capacitors under no load at 85°C for 1000 hours and then performing voltage treatment based on JIS C 5101-4 clause 4.1 at 20°C, they shall meet the specified values for the endurance characteristics listed above.										
Resistance to soldering heat	The capacitors are kept on a hot plate for 30 seconds, which is maintained at 250°C. The capacitors shall meet the characteristic requirements listed at right when they are removed from the plate and restored to 20°C.						Capacitance change		Within ±10% of the initial capacitance value		
							tan δ		Less than or equal to the initial specified value		
							Leakage current		Less than or equal to the initial specified value		
Marking	Black print on the case top.										


Chip Type



Type numbering system (Example : 10V 100μF)



(φ8 × 10, φ10)



φ D × L	6.3 × 5.8	6.3 × 7.7	8 × 6.2	8 × 10	10 × 10
A	2.4	2.4	3.3	2.9	3.2
B	6.6	6.6	8.3	8.3	10.3
C	6.6	6.6	8.3	8.3	10.3
E	2.2	2.2	2.3	3.1	4.5
L	5.8	7.7	6.2	10	10
H	0.5 to 0.8	0.5 to 0.8	0.5 to 0.8	0.8 to 1.1	0.8 to 1.1

• Dimension table in next page.

UUR

■ Dimensions

V		4	6.3	10	16	25	35	50	63	100
Cap.(μF)	Code	0G	0J	1A	1C	1E	1V	1H	1J	2A
3.3	3R3									6.3×5.8 29
4.7	4R7								6.3×5.8 31	● 8×6.2 40 (35)
10	100								8×6.2 46	8×10 77
22	220							6.3×5.8 45	8×10 96	8×10 100
33	330						6.3×5.8 55	○ 8×6.2 95 (94)	8×10 117	10×10 130
47	470					6.3×5.8 65	● 8×6.2 105 (94)	○ 8×10 140 (105)	8×10 140	10×10 155
100	101			6.3×5.8 70	8×6.2 125	○ 8×6.2 145 (143)	○ 8×10 175 (132)	■ 10×10 195 (181)	10×10 232	
150	151			6.3×5.8 85	6.3×7.7 151	8×10 192	8×10 214	10×10 238		
220	221		● 8×6.2 160 (143)	○ 8×6.2 175 (173)	○ 8×10 215 (162)	■ 10×10 250 (232)	■ 10×10 265 (246)	10×10 289		
330	331	6.3×5.8 152	○ 8×6.2 190 (188)	8×10 240	8×10 270	■ 10×10 305 (284)	10×10 324			
470	471	6.3×7.7 200	8×10 265	8×10 290	■ 10×10 330 (307)	10×10 393				
680	681	8×10 284	8×10 318	10×10 374	10×10 396					
1000	102	8×10 344	■ 10×10 400 (372)	10×10 454						
1500	152	10×10 347	10×10 489							
									Case size φD × L (mm)	Rated ripple

Size φ6.3 × 5.8 is available for capacitors marked. "●"

Size φ6.3 × 7.7 is available for capacitors marked. "○"

Size φ8 × 10 is available for capacitors marked. "■"

※ In this case, [6] will be put at 12th digit of type numbering system.

Rated ripple current (mArms) at 85°C 120Hz

● Frequency coefficient of rated ripple current

Cap.(μF)	Frequency	50 Hz	120 Hz	300 Hz	1 kHz	10 kHz or more
Less than 47		0.80	1.00	1.15	1.40	1.67
100 to 1500		0.85	1.00	1.08	1.20	1.30

- Taping specifications are given in page 23.
- Recommended land size, soldering by reflow are given in page 18, 19.
- Please select UUG(p.160) if high CV products are required.
- Please refer to page 3 for the minimum order quantity.