



THREADED STANDOFFS



HEX



ROUND



MATERIAL

Brass: per ASTM-B16

Aluminum: QQ-A-225/3, Alloy 2011-T3

PLATING

Zinc: ASTM B633

Iridite Finish: MIL-C-5541

			ALUMINUM IRIDITE FINISH		BRASS ZINC PLATE	
			HEX	ROUND	HEX	ROUND
THREAD	O.D.	LENGTH	CAT. NO.	CAT. NO.	CAT. NO.	CAT. NO.
2-56	.156 (5/32)	3/16 (.187)	1797A	1801A	1798A	1802A
		1/4 (.250)	1797B	1801B	1798B	1802B
		5/16 (.312)	1797C	1801C	1798C	1802C
		3/8 (.375)	1797D	1801D	1798D	1802D
4-40	.187 (3/16)	1/4 (.250)	1891	2025	1450	1547
		3/8 (.375)	1892	2026	1803	1864
		1/2 (.500)	1893	2027	1656	1657
		5/8 (.625)	1894	2028	1804	1865
		3/4 (.750)	1895	2029	1656A	1657A
		7/8 (.875)	1896	2030	1805	1866
		1 (1.000)	1897	2031	1656B	1657B
4-40	.250 (1/4)	1/4 (.250)	2201	3478	1450A	1547A
		3/8 (.375)	2202	3479	1450B	1547B
		1/2 (.500)	2203	3480	1450C	1547C
		5/8 (.625)	1808	1839	1829	1867
		3/4 (.750)	2204	3481	1450D	1547D
		7/8 (.875)	1809	1846	1830	1876
		1 (1.000)	2205	3482	1450E	1547E
		1-1/2 (1.500)	2206	3483	1831	1877
		2 (2.000)	2207	3484	1832	1878
6-32	.250 (1/4)	1/4 (.250)	2208	3485	1451A	1548A
		3/8 (.375)	2209	3486	1451B	1548B
		1/2 (.500)	2210	3487	1451C	1548C
		5/8 (.625)	1813	1847	1451D	1548D
		3/4 (.750)	2211	3488	1451E	1548E
		7/8 (.875)	1816	1848	1833	1879
		1 (1.000)	2212	3489	1635	1548F
		1-1/4 (1.250)	1818	1853	1636	1881
		1-1/2 (1.500)	2213	3490	1637	1882
		1-3/4 (1.750)	1819	1855	1638	1883
		2 (2.000)	2214	3491	1639	1884
		2-1/4 (2.250)	1820	1856	1642	1885
		2-1/2 (2.500)	1825	1857	1643	1886
8-32	.250 (1/4)	1/4 (.250)	2215	3492	1474A	1692A
		3/8 (.375)	2216	3493	1474B	1692B
		1/2 (.500)	2217	3494	1474C	1692C
		5/8 (.625)	1827	1858	1834	1887
		3/4 (.750)	2218	3495	1474D	1692D
		7/8 (.875)	1828	1859	1836	1888
		1 (1.000)	2219	3496	1474E	1692E
		1-1/2 (1.500)	2220	3497	1837	1889
		2 (2.000)	2221	3498	1838	1899
8-32	.375 (3/8)	3/8 (.375)	1926A	2315A	1452A	1549A
		1/2 (.500)	1926B	2315B	1452B	1549B
		5/8 (.625)	1926C	2315C	1452C	1549C
		3/4 (.750)	1926D	2315D	1452D	1549D
		1 (1.000)	1926E	2315E	1452E	1549E

NOTE: Spacers over 1.000 long are tapped .375 deep each end.