

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT -

BY - TE CONNECTIVITY



ALL RIGHTS RESERVED.

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	F2	REVISED PER ECR-17-008062	05JUN2017	BW	FV

CRIMPING DATA

F	.280	.150-.250, (2).125	F	.140	.067	(1)16 OR (2)18	D	16-12, (2)16, (2)18	.855	A1 8039
					.073	14	C			
					.078	(2)16	B			
					.084	12	A			
TYPE	SIZE	INSULATION RANGE	TYPE	SIZE	CRIMP HEIGHT	WIRE SIZE	PAO LTR	WIRE RANGE		
INSULATION BARREL CRIMP			WIRE BARREL CRIMP						FEED	APPL INST




SECTION A - A



SECTION B - B

WIRE SIZE	INSUL SIZE(2)
16-12	Ø.125

NICKEL PLATED STEEL	640253-4
REELED WITH "U"S UP	640253-2
REELED WITH "U"S UP	640253-1
PLATING	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN -	 TE Connectivity							
		CHK -								
		APVD -								
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME RING						
		0 PLC ±-		PRODUCT SPEC -						
		1 PLC ±-								
		2 PLC ±-								
		3 PLC ±.015								
4 PLC ±-		APPLICATION SPEC -		SIZE CAGE CODE DRAWING NO RESTRICTED TO						
ANGLES ±-		WEIGHT -						A300779C-640253		
MATERIAL .018 BRASS -		FINISH TIN -		CUSTOMER DRAWING				SCALE 5:1	SHEET 1 OF 1	REV F2