

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
FED. MFR. CODE 91929

SWITCH-ENCLOSED

CATALOG LISTING
OPH-AR5

OPH-AR5

M

DRAWING
NUMBER

ISSUE

3

3

3

3

3

3

3

3

3

3

3

3

3

3

3

3

3

3

3

3

3

3

3

3

3

3

3

3

3

REPLACES

SR 8924


CHECK

CHECK

CHECK

CHECK


MTG HOLE AND SLOT FOR .250 DIA SCREW
HOLE FOR NO. 10 PAN HEAD SCREW (6)



MOUNTING BRACKET (1) AND 10-32 UNF X .250 REF
PAN HEAD SCREW (2) FURNISHED UNASSEMBLED
SCALE - HALF SIZE

(3) NO. 18 WIRE LEAD PER MIL-W-5086
MARKED PER MIL-W-5088


ROLLER LEVER
ADJUSTABLE THRU
360°



LEADS PROJECT 9.0 MIN
BEYOND OUTLET


RIGHT HAND
CLOCKWISE
ROTATION

ROLLER LEVER MAY BE POSITIVELY LOCKED
AT INTERVALS OF APPROX 0.2°
(1980 POSITIONS)



.750 REF DIA X .250 REF WIDE
STEEL ROLLER

MOUNTING HOLE IN
OPPOSITE WALL (2)



10-32 NF LOCKING
TYPE NUT .375 REF
ACROSS FLATS

CAPTIVE COVER SCREW (4)

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	
OPERATING FORCE	8-24 OZ
RELEASE FORCE	4 OZ MIN
PRETRAVEL	8° (219 MAX)
DIFFERENTIAL TRAVEL	.025 MAX
DO NOT OVERTRAVEL MORE THAN 25°	
SWITCH-BASIC REPLACEMENT-4HS201-118	

ELECTRICAL DATA	
CONTACT ARRANGEMENT	S P D T

SCALE FULL	
DO NOT SCALE PRINT	
UNLESS OTHERWISE SPECIFIED	
DIMENSIONS ARE IN INCHES	
TOLERANCES ARE:	
ONE PLACE	(.0) ± .030
TWO PLACE	(.00) ± .015
THREE PLACE	(.000) ± .008
ANGLES	±
WEIGHT	

NOTE-

- 1- MOUNTING SCREW HOLE, 10-32 NF-28 THREADS X .219 REF DEEP. (8)
- 2- SEALED CONSTRUCTION PROVIDES SPLASH RESISTANCE
- 3- LEADS APPROPRIATELY MARKED FOR CIRCUIT IDENTIFICATION