


REVISIONS				
ZONE	REV	DESCRIPTION	DATE	APPROVED
	A	New Release	10/26/04	H.T.



PIN ASSIGNMENT		
P1	P2	
1	2	RED
3	1	WHITE
2	3	SHIELD
4	10	GREEN
6	9	WHITE
5	11	SHIELD
7	18	BLUE
9	17	WHITE
8	19	SHIELD
10	23	BROWN
12	24	WHITE
11	22	SHIELD
15	6	VIOLET
16	7	RED
17	15	ORANGE
18	14	YELLOW
19	16	WHITE
SHIELD	SHIELD	

PART NO.	CABLE LENGTH
10HM-15128-01	1 m
10HM-15128-02	2 m
10HM-15128-03	3 m
10HM-15128-05	5 m

ITEM NO.	MATERIAL / SPECIFICATION	QTY	UNIT
6.	UL 1061 26AWG. INSULATOR WIRE, LENGTH 28mm	1	PCS.
	BLACK HEAT SHRINK TUBE #1.0x8mm	17	PCS.
	BLACK HEAT SHRINK TUBE #3.0x6mm	4	PCS.
	BLACK HEAT SHRINK TUBE #0.8x10mm	4	PCS.
	COPPER FOIL 7.5x25mm	1	PCS.
	COPPER FOIL 33x90mm	1	PCS.
	MOLDED PE COLOR TRANSPARENT		
	BLACK PVC MOLDED HOOD		
5.	BLACK PVC TUBE #3.0x6mm	4	PCS.
	BLACK PVC TUBE #0.8x10mm	4	PCS.
	COPPER FOIL 15x60mm	1	PCS.
	MOLDED PE COLOR TRANSPARENT		
	MOLDED PVC BLACK		
4.	UL 20276 [(2BAWGx1PAIR+D+FAM)x4PCS+(2BAWGx1PAIR)+(2BAWGx3C)]+AM+B DVI CABLE, O.D. 7.3mm, BLACK PVC OUTER JACKET	XX	M
3.	BLACK PVC MOLDED THUMBSCREW #4-40, LENGTH 46.5mm	2	PCS.
2.	DVI 19 MALE, GOLD PLATED ON CONTACTS & METAL HOOD	1	PCS.
1.	HDMI 19 MALE, GOLD PLATED ON CONTACTS & METAL HOOD	1	PCS.
MATERIAL / SPECIFICATION		QTY	UNIT
CABLE ASSEMBLY PARTS LIST			

UNLESS OTHERWISE SPECIFIED: 1. DIMENSIONS ARE IN INCHES 2. TOLERANCES: DECIMALS ±.XX ±0.25 3. DO NOT SCALE DRAWING 4. REMOVE ALL BURRS AND BREAK SHARP EDGES. PROPRIETARY DOCUMENT THIS DRAWING AND/OR INFORMATION OR SUBJECT MATTER CONTAINED HEREIN, SHALL NOT BE USED, COPIED OR REPRODUCED IN ANY MANNER, OR FOR ANY PURPOSE, OTHER THAN AS EXPRESSLY SHOWN BY COMTOP Enterprises Corp.	CUSTOMER	268 Benton Ct. Industry, CA 91789 Tel.: 909-468-5737. Fax: 909-468-5726		
	CUSTOMER APPROVAL		TITLE HDMI MALE / DVI MALE CABLE ASSEMBLY	
DRAWN Howie Tseng	DATE 10/26/04	SIZE FSCM NO. 10HM-15128	DWG NO. 10HM-15128-xx	REV A
CHECKED		SCALE NONE	Release Date: 10/26/04	SHEET 1 OF 1