








SEE SHEET 2 FOR NOTES



OBSELETE, SUPERSEDED BY -4 -
SUPERSEDED BY 5145165-2
OBSELETE -


		W		FINISH		PART NUMBER							
S A CONTROLLED DOCUMENT.		DWN R BROWN 6/12/95 CHK M BOWERS 6/12/95		 TE Connectivity									
TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APVD —		NAME									
0 PLC ± — 1 PLC ± — 2 PLC ± 0.25[.01] 3 PLC ± 0.13[.005] 4 PLC ± — ANGLES ± 2° FINISH		PRODUCT SPEC 108—14034 APPLICATION SPEC 114—26012		CONNECTOR ASSEMBLY, 92 DUAL POSITION, .050 SERIES,									
		WEIGHT —		SIZE A1		CAGE CODE 00779		DRAWING NO C=145165		RESTRICTED TO —			
		CUSTOMER DRAWING						SCALE 4:1		SHEET 1 OF 2		REV H2	

D


C

B

A



RECOMMENDED CONNECTOR MOUNTING HOLE PATTERN
(CONNECTOR SIDE SHOWN)



RECOMMENDED MATING BOARD EDGE CONFIGURATION

- 1 HOUSING: HIGH TEMPERATURE THERMOPLASTIC.
COLOR - NATURAL
- 2 CONTACT: PHOSPHOR BRONZE.
- 3 CONTACT FINISH: 0.00127[.000050] MIN NICKEL ALL OVER.
GOLD FLASH OVER NICKEL IN CONTACT AREA.
0.00254[.000100] MIN TIN-LEAD OVER NICKEL ON SOLDER TAILS.
- 4 CONTACT FINISH: 0.00127[.000050] MIN NICKEL ALL OVER.
0.00038[.000015] GOLD OVER NICKEL IN CONTACT AREA.
0.00254[.000100] MIN TIN-LEAD OVER NICKEL ON SOLDER TAILS.
- 5 CONTACT FINISH: 0.00127[.000050] MIN NICKEL ALL OVER.
0.00076[.000030] GOLD OVER NICKEL IN CONTACT AREA.
0.00254[.000100] MIN TIN-LEAD OVER NICKEL ON SOLDER TAILS.
- 6 DISTANCE FROM CONTACT POINT TO BOTTOM OF CARD SLOT.
- 7 AMP PART NUMBER, DATE CODE AND CSA LOGO MARKED IN APPROXIMATE LOCATION SHOWN.
- 8 CORED OR SOLID SIDE WALLS ARE AT DISCRETION OF AMP INCORPORATED.
- 9 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
R BROWN
6/12/95

CHK
M BOWERS
6/12/95

REV
1
6/12/95

DIMENSIONS:
mm [INCHES]

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± .005
1 PLC ± .005
2 PLC ± .005
3 PLC ± .005
4 PLC ± .005
ANGLES ± .2°

MATERIAL
SEE SHEET 1

FINISH
SEE SHEET 1

WEIGHT
—

CUSTOMER DRAWING

NAME
CONNECTOR ASSEMBLY,
92 DUAL POSITION,
.050 SERIES,

SIZE
A1

CAGE CODE
00779

DRAWING NO
145165

RESTRICTED TO
—

SCALE
4:1

SHEET
2

OF
2

REV
H2