


NO	DESCRIPTION	DATE
①	MODIFICATION CENTER CONTACT ② BACKGROUND FORMAT UPDATED	01.21.10'



1.0 ELECTRICAL

- 1.1 FREQUENCY RANGE: DC-900 MHz
1.2 NOMINAL IMPEDANCE: 50 OHM

2.0 MATERIALS

- 2.1 BODIES: BRASS PER JIS-C3604
2.2 CENTER CONTACT: BERYLLIUM COPPER PER ASTM B196 UNS C17300
2.3 INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710

3.0 FINISHES AND OTHERS

- 3.1 SEE BELOW TABLE FOR DETAILS.

4.0 ENVIRONMENTAL

- 4.1 OPERATING TEMPERATURE RANGE: -55° C TO +125° C

4	BODY	BRASS	1	NICKEL 100μ" MIN.
3	INSULATION	TEFLON	1	NONE
2	CENTER CONTACT	BERYLLIUM COPPER	1	GOLD
1	INSULATION	TEFLON	1	NONE
NO	DESCRIPTION	MATERIAL	Q'TY	FINISH

APPROVED by _____ DATE: _____

DESCRIPTION		FME PLUG TO SMA JACK							
製圖	DRAWN	TOLERANCE		品名	23-04	T.G.N	日期	DATE	版次
	Yoko			TITLE	\ROHS COMPLIANT <50Ω>		04.26.93		A-1
檢圖	CHECK	.XX ±0.1		單位	UNIT	DWG.NO. 23-0023			
	Jacky			比例	SCALE				
認定	APPROVAL	.XXX ±0.05		比	SCALE	佳楠精密電子股份有限公司 CHIN NAN PRECISION ELECTRONICS CO.,LTD.			
	Lewis	ANGLE ±5°		例	4:1				