




REV. 0

DCO 170339


COIL: @ 25°C
 RESISTANCE $2500 \text{ OHMS} \pm 10\%$
 NOMINAL VOLTAGE 8.0 mADC
 MUST OPERATE 4.0 mADC
 MUST RELEASE $2.0 \text{ mADC MAX } 0.40 \text{ mADC MIN}$

ENVIRONMENT:

VIBRATION $10 \text{ CPS TO } 2000 \text{ CPS @ } 15 \text{ g's}$
 SHOCK $100 \text{ g's } 6 \text{ MS. DURATION}$
 TEMPERATURE $-65^{\circ}\text{C TO } +125^{\circ}\text{C}$

NOTES: OPERATE TIME 15 MS MAX
RELEASE TIME 10 MS MAX
CONTACT BOUNCE 2 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO
2 AMPS 28 VDC RESISTIVE
100,000 OPERATIONS

DR. PBB 12/6/00

CK. TLG 12-11-00

CII Technologies™
 advanced control electronic solutions

CUST. QPL

CUST. NO. M5757/13-140 REV.

3SAT RELAY

3SAT1357A2