


**— NEW —**

|                                          |      |      |                                          |      |       |
|------------------------------------------|------|------|------------------------------------------|------|-------|
| 863-0050, 44050-0001, Unshielded, 1-49   | EACH | 2.31 | 863-0053, 44150-0002, Snap fit pgs. 1-49 | EACH | 9.11  |
| 50-99                                    | EACH | 2.08 | 50-99                                    | EACH | 8.20  |
| 100-499                                  | EACH | 1.73 | 100-499                                  | EACH | 6.83  |
| 863-0051, 44050-0006, Shielded, 1-49     | EACH | 3.58 | 863-0054, 44150-0005, Snap fit pgs. 1-49 | EACH | 8.66  |
| 50-99                                    | EACH | 3.22 | 50-99                                    | EACH | 7.79  |
| 100-499                                  | EACH | 2.69 | 100-499                                  | EACH | 6.49  |
| 863-0052, 44150-0001, Snap fit pgs. 1-49 | EACH | 5.39 | 863-0055, 44150-0006, Snap fit pgs. 1-49 | EACH | 14.30 |
| 50-99                                    | EACH | 4.86 | 50-99                                    | EACH | 12.87 |
| 100-499                                  | EACH | 4.05 | 100-499                                  | EACH | 10.73 |

## Avikrimp® Fully Insulated Quick Disconnects —NEW—



| Stock No. | Mfr.'s Type | Color  | Wire AWG | Tab Size      | PER PK./100 |       |       |
|-----------|-------------|--------|----------|---------------|-------------|-------|-------|
|           |             |        |          |               | 1-9         | 10-24 | 25-99 |
| 863-3203  | AA-5261     | Red    | 22-18    | 0.250 x 0.032 | 17.68       | 15.91 | 13.26 |
| 863-3202  | AA-5267     | Red    | 22-18    | 0.187 x 0.020 | 30.87       | 29.58 | 24.65 |
| 863-3204  | AA-5275     | Red    | 22-18    | 0.110 x 0.020 | 32.67       | 27.34 | 24.78 |
| 863-3205  | BB-5263     | Blue   | 16-14    | 0.250 x 0.032 | 22.44       | 18.70 | 17.26 |
| 863-3206  | BB-5269     | Blue   | 16-14    | 0.187 x 0.020 | 22.40       | 20.20 | 16.63 |
| 863-3207  | BB-5277     | Blue   | 16-14    | 0.110 x 0.020 | 31.73       | 28.56 | 23.80 |
| 863-3208  | C-5265      | Yellow | 12-10    | 0.250 x 0.032 | 36.49       | 32.84 | 27.37 |

|                 |         |        |       |                      |              |              |              |
|-----------------|---------|--------|-------|----------------------|--------------|--------------|--------------|
| <b>863-3209</b> | AA-5260 | Red    | 22-18 | $0.250 \times 0.032$ | <b>38.76</b> | <b>34.88</b> | <b>29.07</b> |
| <b>863-3210</b> | AA-5266 | Red    | 22-18 | $0.187 \times 0.020$ | <b>37.40</b> | <b>33.66</b> | <b>28.05</b> |
| <b>863-1246</b> | BB-5262 | Blue   | 16-14 | $0.250 \times 0.032$ | <b>34.88</b> | <b>29.07</b> | <b>24.92</b> |
| <b>863-3211</b> | BB-5268 | Blue   | 16-14 | $0.187 \times 0.020$ | <b>33.09</b> | <b>29.78</b> | <b>24.82</b> |
| <b>863-3212</b> | C-5264  | Yellow | 12-10 | $0.250 \times 0.032$ | <b>37.17</b> | <b>33.46</b> | <b>27.88</b> |

|                                                     |                    |             |
|-----------------------------------------------------|--------------------|-------------|
| <b>Nylon Insulated</b>                              |                    |             |
| <b>Type NC-2212. 2 #16 max. and 2 #22 min. AWG.</b> |                    |             |
| <b>863-1241. NC-2212. 1-9</b>                       | <b>PER PK./100</b> | <b>5.89</b> |
| <b>Type NC-1610. 2 #12 max. and 4 #18 min. AWG.</b> |                    |             |
| <b>863-1242. NC-1610. 1-9</b>                       | <b>PER PK./100</b> | <b>8.16</b> |

**Type ABC-500.** For use with 22-AWG through 10-AWG, cuts and strips wire, cuts and rethreads bolts. Constructed of tempered steel alloy.

**863-1250.** ABC-500 ..... **EACH 24.28**

|                                                                         |            |
|-------------------------------------------------------------------------|------------|
| Type K-130. Deluxe non-insulated and insulated solderless terminal kit. |            |
| 863-1260. K-130 .....                                                   | EACH 42.42 |
| Type K-140. Deluxe insulated solderless terminal kit.                   |            |
| 863-1270. K-140 .....                                                   | EACH 47.52 |

| Vinyl Insulated |           |            |            |                       |
|-----------------|-----------|------------|------------|-----------------------|
| 863-1200        | A-232-06X | #6 Stud.   | 22-18 AWG. | 1-9 PER PK./100 7.03  |
| 863-1201        | A-221-08X | #6 Stud.   | 22-18 AWG. | 1-9 PER PK./100 7.03  |
| 863-1202        | B-237-06X | #6 Stud.   | 16-14 AWG. | 1-9 PER PK./100 7.03  |
| 863-1203        | B-237-08X | #6 Stud.   | 16-14 AWG. | 1-9 PER PK./100 7.03  |
| 863-1204        | B-237-10X | #10 Stud.  | 16-14 AWG. | 1-9 PER PK./100 7.03  |
| 863-1205        | C-228-08X | #8 Stud.   | 12-10 AWG. | 1-9 PER PK./100 9.29  |
| 863-1206        | C-228-10X | #10 Stud.  | 12-10 AWG. | 1-9 PER PK./100 9.29  |
| 863-1207        | C-230-14X | #1/4 Stud. | 12-10 AWG. | 1-9 PER PK./100 10.65 |

**Nylon Insulated**

|           |            |           |            |     |             |       |
|-----------|------------|-----------|------------|-----|-------------|-------|
| 863-1208. | AA-832-06. | #6 Stud.  | 22-18 AWG. | 1-9 | PER PK./100 | 10.88 |
| 863-1209. | AA-821-08. | #8 Stud.  | 22-18 AWG. | 1-9 | PER PK./100 | 10.88 |
| 863-1210. | BB-837-06. | #6 Stud.  | 16-14 AWG. | 1-9 | PER PK./100 | 10.88 |
| 863-1211. | BB-837-08. | #8 Stud.  | 16-14 AWG. | 1-9 | PER PK./100 | 10.20 |
| 863-1212. | BB-837-10. | #10 Stud. | 16-14 AWG. | 1-9 | PER PK./100 | 10.88 |
| 863-1214. | C-829-10.  | #10 Stud. | 12-10 AWG. | 1-9 | PER PK./100 | 14.28 |

|                        |                   |                                 |                          |
|------------------------|-------------------|---------------------------------|--------------------------|
| <b>Nylon Insulated</b> |                   |                                 |                          |
| <b>863-1224.</b>       | <b>AA-838-06.</b> | <b>#6 Stud. 22-18 AWG. 1-9</b>  | <b>PER PK./100 10.88</b> |
| <b>863-1225.</b>       | <b>AA-834-08.</b> | <b>#8 Stud. 22-18 AWG. 1-9</b>  | <b>PER PK./100 10.88</b> |
| <b>863-1227.</b>       | <b>C-841-08.</b>  | <b>#8 Stud. 12-10 AWG. 1-9</b>  | <b>PER PK./100 13.37</b> |
| <b>863-1228.</b>       | <b>C-841-10.</b>  | <b>#10 Stud. 12-10 AWG. 1-9</b> | <b>PER PK./100 14.05</b> |

|                                                |             |      |  |
|------------------------------------------------|-------------|------|--|
| <b>Butt Splices</b>                            |             |      |  |
| <b>Vinyl Insulated</b>                         |             |      |  |
| 863-1229. A-245X. Fig. C. 22-18 AWG. 1-9 ..... | PER PK./100 | 6.12 |  |
| 863-1230. B-231X. Fig. C. 16-14 AWG. 1-9 ..... | PER PK./100 | 6.12 |  |
| 863-1231. C-246X. Fig. C. 12-10 AWG. 1-9 ..... | PER PK./100 | 8.61 |  |

|                        |                                         |                          |
|------------------------|-----------------------------------------|--------------------------|
| <b>Nylon Insulated</b> |                                         |                          |
| <b>863-1232.</b>       | <b>AS-N-345, Fig. D, 22-18 AWG, 1-9</b> | <b>PER PK./100 7.03</b>  |
| <b>863-1233.</b>       | <b>BS-N-331, Fig. D, 16-14 AWG, 1-9</b> | <b>PER PK./100 7.03</b>  |
| <b>863-1234.</b>       | <b>CS-N-346, Fig. D, 12-10 AWG, 1-9</b> | <b>PER PK./100 14.05</b> |

|                 |             |                           |                   |
|-----------------|-------------|---------------------------|-------------------|
| Vinyl Insulated |             |                           |                   |
| 863-1216.       | A-238-06X.  | #6 Stud. 22-18 AWG. 1-9   | PER PK./100 7.03  |
| 863-1217.       | A-234-08X.  | #8 Stud. 22-18 AWG. 1-9   | PER PK./100 7.03  |
| 863-1218.       | B-2781-06X. | #6 Stud. 16-14 AWG. 1-9   | PER PK./100 6.68  |
| 863-1219.       | B-2781-08X. | #8 Stud. 16-14 AWG. 1-9   | PER PK./100 7.03  |
| 863-1221.       | C-241-08X.  | #8 Stud. 12-10 AWG. 1-9   | PER PK./100 7.48  |
| 863-1222.       | C-241-10X.  | #10 Stud. 12-10 AWG. 1-9  | PER PK./100 7.93  |
| 863-1223.       | C-268-14X.  | #1/4 Stud. 12-10 AWG. 1-9 | PER PK./100 10.20 |

**Nylon Insulated**  
**Type AA-8140.** 22-18 AWG. .250 x .032 tab size.  
**863-1235. AA-8140. 1-9** ..... **PER PK./100 10.43**  
**Type BB-8141.** 16-14 AWG. .250 x .032 tab size.  
**863-1236. BB-8141. 1-9** ..... **PER PK./100 10.43**

**Nylon Insulated**

|                                                        |             |       |
|--------------------------------------------------------|-------------|-------|
| 863-1237. AA-2260. Fig. F. Male. 22-18 AWG. 1-9.....   | PER PK./100 | 12.47 |
| 863-1238. BB-2262. Fig. F. Male. 16-14 AWG. 1-9.....   | PER PK./100 | 12.47 |
| 863-1239. AA-2201. Fig. G. Female. 22-18 AWG. 1-9..... | PER PK./100 | 12.69 |
| 863-1240. BB-2206. Fig. G. Female. 16-14 AWG. 1-9..... | PER PK./100 | 12.69 |

The Micro-Fit 3.0™ is a unique interconnect system designed to meet the need for a rugged signal connector, and incorporates many of the features previously found only on large power connectors.


| Panel Mount |             | Free Hanging |             | No. of Circuits | Dimensions (In.) |       |       | EACH  |         |           |
|-------------|-------------|--------------|-------------|-----------------|------------------|-------|-------|-------|---------|-----------|
| Stock No.   | Mfr.'s Type | Stock No.    | Mfr.'s Type |                 | A                | B     | C     | 1-499 | 500-999 | 1000-2499 |
| 863-0501    | 43020-0200  | —            | —           | 2               | 0.152            | —     | 0.161 | .26   | .23     | .20       |
| 863-0502    | 43020-0400  | 863-0503     | 43020-0401  | 4               | 0.270            | 0.118 | 0.279 | .38   | .34     | .29       |
| 863-0504    | 43020-0600  | 863-0505     | 43020-0601  | 6               | 0.388            | 0.236 | 0.397 | .46   | .41     | .34       |
| 863-0506    | 43020-0800  | 863-0507     | 43020-0801  | 8               | 0.505            | 0.354 | 0.515 | .51   | .47     | .31       |
| 863-0508    | 43020-1000  | 863-0509     | 43020-1001  | 10              | 0.622            | 0.472 | 0.631 | .50   | .45     | .37       |
| —           | —           | 863-0496     | 43020-1201  | 12              | 0.742            | 0.591 | 0.751 | .57   | .51     | .43       |
| 863-0512    | 43020-1400  | 863-0513     | 43020-1401  | 14              | 0.860            | 0.709 | 0.869 | .67   | .60     | .50       |
| —           | —           | 863-0497     | 43020-1601  | 16              | 0.978            | 0.827 | 0.987 | .77   | .70     | .58       |
| 863-0516    | 43020-1800  | 863-0517     | 43020-1801  | 18              | 1.096            | 0.945 | 1.105 | .87   | .78     | .65       |
| 863-0518    | 43020-2000  | 863-0519     | 43020-2001  | 20              | 1.215            | 1.063 | 1.223 | .97   | .87     | .72       |
| —           | —           | 863-0521     | 43020-2201  | 22              | 1.333            | 1.181 | 1.341 | 1.06  | .95     | .79       |
| 863-0522    | 43020-2400  | 863-0523     | 43020-2401  | 24              | 1.451            | 1.299 | 1.459 | 1.16  | 1.04    | .87       |

\*Use male terminal 43031-XXXX.

| Stock No. | Mfr.'s Type | No. of Circuits | Dimensions (In.) |       | EACH  |         |           |
|-----------|-------------|-----------------|------------------|-------|-------|---------|-----------|
|           |             |                 | A                | B     | 1-499 | 500-999 | 1000-2499 |
| 863-0524  | 43025-0200  | 2               | 0.152            | —     | .26   | .23     | .20       |
| 863-0525  | 43025-0400  | 4               | 0.270            | 0.118 | .36   | .34     | .29       |
| 863-0526  | 43025-0600  | 6               | 0.388            | 0.236 | .46   | .42     | .35       |
| 863-0527  | 43025-0800  | 8               | 0.506            | 0.354 | .46   | .36     | .30       |
| 863-0528  | 43025-1000  | 10              | 0.624            | 0.472 | .55   | .50     | .41       |
| 863-0529  | 43025-1200  | 12              | 0.742            | 0.591 | .59   | .53     | .45       |
| 863-0547  | 43025-1400  | 14              | 0.860            | 0.709 | .68   | .61     | .51       |
| 863-0531  | 43025-1600  | 16              | 0.978            | 0.827 | .78   | .70     | .58       |
| 863-0532  | 43025-1800  | 18              | 1.096            | 0.945 | .88   | .78     | .65       |
| 863-0533  | 43025-2000  | 20              | 1.215            | 1.063 | 1.02  | .92     | .77       |
| 863-0534  | 43025-2200  | 22              | 1.333            | 1.181 | 1.46  | 1.31    | 1.10      |
| 863-0535  | 43025-2400  | 24              | 1.451            | 1.299 | 1.18  | 1.06    | .88       |

†Use female terminals 43030-XXXX.

|                                             |      |       |
|---------------------------------------------|------|-------|
| 863-0546. 11-03-0043. Extraction tool ..... | EACH | 28.25 |
|---------------------------------------------|------|-------|



| Stock No. | Mfr.'s Type | Description | Wire AWG | Plating | EACH   |           |
|-----------|-------------|-------------|----------|---------|--------|-----------|
|           |             |             |          |         | 1-4999 | 5000-9999 |
| 863-0536  | 43031-0007  | Male        | 20-24    | Tin     | .10    | .09       |
| 863-0537  | 43030-0007  | Female      | 20-24    | Tin     | .12    | .11       |
| 863-0538  | 43031-0010  | Male        | 26-30    | Tin     | .10    | .09       |
| 863-0539  | 43030-0010  | Female      | 26-30    | Tin     | .10    | .09       |
| 863-0555  | 43031-0009  | Male        | 26-30    | Gold†   | .15    | .14       |
| 863-0541  | 43030-0009  | Female      | 26-30    | Gold†   | .13    | .12       |
| 863-0542  | 43031-0012  | Male        | 26-30    | Gold†   | .16    | .14       |
| 863-0543  | 43030-0012  | Female      | 26-30    | Gold†   | .15    | .14       |