

Home: >

Part Number: 44483-0006

MINIFIT BMI RA HDR 30AU 12CKT/VOIDS

Image not available

Status: OBSOLETE
Replacement: Contact Molex
Series: 44483
Category: Molex Parts

CHECK DISTRIBUTOR INVENTORY
Add to My Parts

Go to Part Detail

Series image - Reference only

Note - Please disable browser pop-up blockers to view documents on www.molex.com

Product Environmental Compliance

EU ELV:Product not active
EU RoHS:Product not active
EU RoHS Phthalates:Product not active
China RoHS:
REACH SVHC:Product not active
Low-Halogen Status:Product not active

- Product Compliance Statement
- EU RoHS Certificate of Compliance (PDF)
- Multiple Part Product Compliance Statements
EU RoHS, REACH SVHC, & Low-Halogen
- Multiple Part Industry Compliance Documents
*IPC 1752A Class C
*IPC 1752A Class D
*Molex Product Compliance Declaration

Application Tooling FAQ

Tooling specifications and manuals are found by selecting the products below.
Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling
Check our list of old tooling that used to be available for this part

Questions on Product Environmental Compliance? EmailProductCompliance@molex.com
Request Molex's CMRT from conflictminerals@molex.com

Part Detail

COLLAPSE ALL

General

Table with 2 columns: Attribute (Status, Category, Series, UPC) and Value (Obsolete, Molex Parts, 44483, 800754011174)

Physical

Table with 2 columns: Attribute (Flammability, Net Weight) and Value (94V-0, 5.332/g)

Agency Certification

Please find UL Certificates by searching the UL Database using the Molex Series Number.
Click here to visit the UL Database

Table with 2 columns: Agency (CSA, UL) and Certificate Number (LR19980, E29179)

Solder Process Data

Solderability Shelf Life Statement

Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	260

PRODUCTS

[Antennas](#)
[Application Tooling](#)
[Cable Assemblies](#)
[Connected Lighting](#)
[Connectors](#)
[Copper Flex](#)
[Electrical Products](#)
[Industrial Automation](#)
[Membrane Switches](#)
[Optical Solutions](#)
[Printed Electronic Solutions](#)


QUICK LINKS

[Company Information](#)
[Contact Molex](#)
[Cross-Reference](#)
[Koch Industries](#)
[Industries](#)
[Investor Relations](#)
[Literature](#)
[Molex Racing](#)
[Press Room / Press Releases](#)
[Product Index](#)
[Sitemap](#)
[Terms & Conditions](#)

RESOURCES

[Supply Chain Transparency](#)
[Business Continuity](#)
[Compliance](#)
[ecocare](#)
[Feedback | Help](#)
[Jobs](#)
[Legal | Trademarks](#)
[Mobile Site](#)
[Supplier Portal](#)
[Privacy Policy](#)
[Tradeshows](#)

STAY CONNECTED



Molex is a registered trademark of Molex, LLC in the United States of America and may be registered in other countries; all other trademarks listed herein belong to their respective owners.

© Copyright 2017