





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		D2	REVISED PER ECO-11-004835	11MAR11	RK	HMR



SECTION X-X
SCALE 20:1

SECTION Y-Y
SCALE 20:1

- 1 FOR MINI-APPLICATOR AND STRIPPER CRIMPER.
- 2 FOR HAND TOOL USE ONLY.
- 3 WIRE RANGE OF 24-28, INSULATION RANGE OF .030-.040.
- 4 TIN PLATING MAY NOT APPEAR ON CARRIER STRIP.
- 5 GOLD FLASH ON INSIDE OF LOCALIZED GOLD PLATE AREA, .000100 TIN ON CRIMP BARRELS, ALL OVER .000030 NICKEL UNDERPLATE.
- 6 PLATED WITH .000030 GOLD ON INSIDE OF LOCALIZED GOLD PLATE AREA, .000100 TIN ON CRIMP BARRELS, ALL OVER .000050 NICKEL UNDERPLATE.
-OR-
GOLD FLASH OVER PALLADIUM-NICKEL PLATE, .000030 TOTAL ON INSIDE OF LOCALIZED GOLD PLATE AREA, .000100 TIN ON CRIMP BARRELS, ALL OVER .000050 NICKEL UNDERPLATE.
- 7 FOR STANDARD APPLICATOR ONLY.
- 8 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

8 OBSOLETE	5	7	STRIP	1658538—4
	5	1	STRIP	1658538—3
	6	1	STRIP	1658538—2
	5	2	LOOSE PIECE	1658538—1
	FINISH	USE	TYPE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. VARELA - 11-17-04	TE Connectivity			
		CHK J. GERACE - 11-17-04				
		APVD M. WALMSLEY - 11-17-04	NAME			
		PRODUCT SPEC 108-40005	SOCKET CONTACT, 20 DF, 24-28 AWG, AMPLIMITE			
		APPLICATION SPEC 114-10000				
MATERIAL PHOSPHOR BRONZE		WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C-1658538	RESTRICTED TO -
		CUSTOMER DRAWING	SCALE 10:1	SHEET 1 of 1	REV D2	